Adatlap

KOBBS 9.5X50

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- Overpressure valve protects against overloading
- Cylinder head angled at 90°
- Angled head can be rotated through 360°
- Ergonomic handle springs back automatically
- The waste piece no longer becomes jammed thanks to triple splitting
- Hydraulic punch made of high-strength aluminium (approx. 40% weight saving)
- Service life greatly reduced when stainless steel sheets are used

Not suitable for stainless steel!

Általános rendelési adatok

Változat	Lemezlyukasztó
Rendelési szám	9205030000
Típus	KOBBS 9.5X50
GTIN (EAN)	4032248694266
Qty.	1 Darab

KOBBS 9.5X50

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Műszaki adatok

Méretek és tömegek

Magasság	50 mm	Magasság (coll)	1.9685 inch
Átmérő	9.5 mm	Nettó tömeg	63 g

Termékek környezetvédelmi megfelelősége

RoHS megfelelőségi állapot	Nem érintett
REACH SVHC	Lead 7439-92-1
SCIP	6a3438d7-aa8c-48e4-8879-adf736ca79e3

Műszaki adatok

Árucikk leírása	Feszítőcsavar csapágyakkal, 9,5 x 50,0 mm

Besorolások

ETIM 8.0	EC000149	ETIM 9.0	EC000149
ETIM 10.0	EC000149	ECLASS 14.0	21-04-50-03
ECLASS 15.0	21-04-50-03		