
データシート

MHS 6/04-3PM/04 H M4 T3 B T

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

製品イメージ





一般注文データ

バージョン	, オス型ヘッダー, THT/THRはんだ接続, 90°, Tube
注文番号	8000166085
種別	MHS 6/04-3PM/04 H M4 T3 B T
数量	
製品データ	IEC: 1000 V UL:
パッケージ	Tube

データシート

MHS 6/04-3PM/04 H M4 T3 B T

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

技術データ

寸法と重量

深さ	25 mm	奥行き（インチ）	0.9842 inch
高さ	16.6 mm	高さ（インチ）	0.6535 inch
下位バージョンの高さ	13.4 mm	幅	41.625 mm
幅（インチ）	1.6388 inch		

温度

周囲温度	-50 °C…120 °C

材料データ

絶縁材	PA 9T	色	黒色
カラーチャート（類似）	RAL 9011	Moisture Level (MSL)	1
UL 94 可燃性等級	V-0	接点ベース素材	CuMg
接点材質	銅合金	接触表面	錫メッキ
保管温度、最小	-40 °C	保管温度、最大	70 °C
動作温度、最小	-50 °C	動作温度、最大	125 °C

IEC規格に準拠した公称データ

サージ電圧クラス（汚染度 II / 2）の定格電圧	1000 V	サージ電圧クラス（汚染度 III / 2）の定格電圧	160 V
サージ電圧クラス（汚染度 III / 3）の定格電圧	160 V		

重要なメモ

注意事項	• Rated current related to rated cross-section & min. No. of poles. • P on drawing = pitch • Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards. • Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months

分類

ETIM 8.0	EC002637	ETIM 9.0	EC002637
ETIM 10.0	EC002637	ECLASS 14.0	27-46-03-01
ECLASS 15.0	27-46-03-01		

データシート

MHS 6/04-3PM/04 H M4 T3 B T

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

図面

製品イメージ

