


IE-PH-V14M-FO

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Version	Empty enclosure
Order No.	105810000
Type	IE-PH-V14M-FO
GTIN (EAN)	4032248799213
Qty.	10 items

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E316369

Dimensions and weights

Depth	72.45 mm	Depth (inches)	2.8524 inch
Height	26.8 mm	Height (inches)	1.0551 inch
Width	22.3 mm	Width (inches)	0.878 inch
Net weight	56.33 g		

Temperatures

Storage temperature	Operating temperature	-40 °C...70 °C
Installation temperature		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	4f3aae94-c2bc-4010-b63b-5b114ba6bd55

General standards


Connector standard	IEC 61076-3-117 Var. 14	Certificate no. (cULus)	E316369
--------------------	-------------------------	-------------------------	---------

Classifications

ETIM 8.0	EC001031	ETIM 9.0	EC001031
ETIM 10.0	EC001031	ECLASS 14.0	27-19-01-04
ECLASS 15.0	27-19-01-04		

Drawings

Dimensioned drawing



LWL-SC

FO SC inserts for plug-in connectors ver.1 / 4 / 14



General ordering data

Type	IE-PI-SCRJ-SM	Version
Order No.	1067390000	SC insert, Plug SCRJ, singlemode
GTIN (EAN)	4032248820863	
Qty.	10 ST	
Type	IE-PI-SCRJ-MM	Version
Order No.	1067380000	SC insert, Plug SCRJ, multimode
GTIN (EAN)	4032248821129	
Qty.	10 ST	
Type	IE-PI-SCRJ-POF	Version
Order No.	1067410000	SC insert, Plug SCRJ, POF
GTIN (EAN)	4032248820870	
Qty.	10 ST	

Dust caps

For protecting your devices against dust and dirt.




General ordering data

Type	IE-PP-V14P	Version
Order No.	1058280000	Plug housing protective cap
GTIN (EAN)	4032248799374	
Qty.	10 ST	

Accessories

www.weidmueller.com

Blank



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	ESG 9/11 K MC NE WS	Version	
Order No.	1857440000		ESG, Device markers x 11 mm, PA 66, Colour: white, Self-adhesive
GTIN (EAN)	4032248402731		
Qty.	200 ST		