


**IE-PI-SCRJ-MM**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



FO SC inserts for plug-in connectors ver.1 / 4 / 14

**General ordering data**

Version	SC insert, Plug SCRJ, multimode
Order No.	<a href="#">1067380000</a>
Type	IE-PI-SCRJ-MM
GTIN (EAN)	4032248821129
Qty.	10 items
Delivery status	This article will no longer be available in the future.
Last order date	2025-04-08T00:00:00+02:00

## IE-PI-SCRJ-MM

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate No. (UL)	E477798

## Dimensions and weights

Depth	56 mm	Depth (inches)	2.2047 inch
Height	10.5 mm	Height (inches)	0.4134 inch
Width	13.2 mm	Width (inches)	0.5197 inch
Net weight	20.4 g		

## Temperatures

Storage temperature	Operating temperature	-40 °C...70 °C
Installation temperature		

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

## General data

Description of article	Plug SCRJ, multimode	Colour	Miscellaneous
Housing main material	Zinc diecast, PA	Protection degree	IP67 with housing
Plugging cycles	1000	Composition	Connector and flange insert for variant 1, 4 and 14 housings
Fibre type	Multimode	Insertion loss	≤ 0.4 dB
Connection 1	SCRJ	Connection 2	Crimp
Return loss (attenuation)	≥ 30 dB	Ferrule material	Zirconia

## General standards


Connector standard	IEC 61754-24	Certificate No. (UL)	E477798
--------------------	--------------	----------------------	---------

## Classifications

ETIM 8.0	EC001122	ETIM 9.0	EC001122
ETIM 10.0	EC001122	ECLASS 14.0	19-17-01-22
ECLASS 15.0	19-17-01-22		

Drawings

Dimensioned drawing



## IE-PI-SCRJ-MM

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

## Crimp Sets



Crimp sets

## General ordering data

Type	TOOL SET IE-POF	Version	
Order No.	<a href="#">1208930000</a>	Crimping tool: HTX-IE-POF, Stripping tool: Multi-Stripax IE-POF	
GTIN (EAN)	4032248990283		
Qty.	1 ST		

## ...for fibre-optic cable with polymer optical fibres (POF)



Crimping and stripping tools for processing the fibre-optic-cable contacts of polymer optical fibres (POF)

## General ordering data

Type	HTX-IE-POF	Version	
Order No.	<a href="#">1208870000</a>	Pressing tool	
GTIN (EAN)	4032248990269		
Qty.	1 ST		

## ...for fiber-optic connectors SC, ST &amp; LC



## GOF

- For fibre-optic SC/ST, IP 20 and IP 67 connectors
- For fibre-optic LC and IP 67 connectors

## POF

- For polymer fibre-optic SC/ST, IP 20 and IP 67 connectors
- For fibre-optic, Profinet and Mobil cable SC/ST and IP 67 connectors

## General ordering data

Type	IE-CT-SC-GOF	Version	
Order No.	<a href="#">9205320000</a>	Pressing tool, Hexagonal crimp	
GTIN (EAN)	4032248725458		
Qty.	1 ST		

Accessories

Type	IE-CT-SC-GOF-P	Version	
Order No.	<a href="#">9205350000</a>	Pressing tool, Hexagonal crimp	
GTIN (EAN)	4032248725489		
Qty.	1 ST		