


WHP WDL2.5/S BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

Partition plates and end plates are essential accessories for terminal blocks. Partition plates provide optical and electrical separation of different potentials and functional groups, increasing safety and ensuring a clear structure inside the control cabinet. End plates close the terminal block row on the sides, protect against contact with live parts, and ensure a clean, stable finish. Both components are precisely matched to the respective Weidmüller terminal block series, contributing to safe, compliant, and professional wiring.

General ordering data

| | |
|------------|---|
| Version | End and partition plate for terminals, blue, Height: 84.5 mm, Width: 2 mm, V-O, Wemid |
| Order No. | 1067980000 |
| Type | WHP WDL2.5/S BL |
| GTIN (EAN) | 4008 190022440 |
| Qty. | 20 items |

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|----------|-----------------|-------------|
| Depth | 47.95 mm | Depth (inches) | 1.8878 inch |
| Height | 84.5 mm | Height (inches) | 3.3268 inch |
| Width | 2 mm | Width (inches) | 0.0787 inch |
| Net weight | 5.04 g | | |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|----------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -50 °C...75 °C |
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 120 °C |

Environmental Product Compliance

| | | | |
|--------------------------|-----------------------------|------------------|--|
| RoHS Compliance Status | Compliant without exemption | | |
| REACH SVHC | No SVHC above 0.1 wt% | | |
| Product Carbon Footprint | Cradle to gate | 0.054 kg CO2 eq. | |

Material data

| | | | |
|---------------------------|-------|--------|------|
| Basic material | Wemid | Colour | blue |
| UL 94 flammability rating | V-0 | | |

System specifications

| | | | |
|---------|----------------------------|---------------|-------|
| Version | End and intermediate plate | Mounting rail | TS 35 |
|---------|----------------------------|---------------|-------|

Additional technical data

| | | | |
|---------|-----|---------------------|------------------------|
| Snap-on | Yes | Installation advice | Feed-through (bushing) |
|---------|-----|---------------------|------------------------|

Dimensions

| | |
|--------------|-------|
| TS 35 offset | 54 mm |
|--------------|-------|

General

| | | | |
|-----------------|-------|---------------------|------------------------|
| Number of poles | 0 | Installation advice | Feed-through (bushing) |
| Mounting rail | TS 35 | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000886 | ETIM 9.0 | EC000886 |
| ETIM 10.0 | EC000886 | ECLASS 14.0 | 27-25-03-01 |
| ECLASS 15.0 | 27-25-03-01 | | |