


CC 30/60 K MC NE GE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



Similar to illustration



ClipCard device markers in MultiCard format are used for labelling electrical installations and switchgear systems, and offer an interesting alternative to engraving. Thanks to the proven MultiCard format, labelling is possible with PrintJet CONNECT or Plotter.

- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- Universal fixing
- Carrier (screwable or with cable ties)
- Tag rail (self-adhesive or screw fixing)
- Or self-adhesive tags

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | |
|------------|--|
| Version | ClipCard, Device markers, 30 x 60 mm, yellow |
| Order No. | 1078320000 |
| Type | CC 30/60 K MC NE GE |
| GTIN (EAN) | 4032248838370 |
| Qty. | 30 items |

CC 30/60 K MC NE GE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 1.2 mm | Depth (inches) | 0.0472 inch |
| Height | 30 mm | Height (inches) | 1.1811 inch |
| Width | 60 mm | Width (inches) | 2.3622 inch |
| Net weight | 4.46 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -40...60 °C |
|-----------------------------|-------------|

Environmental Product Compliance

| | | |
|--------------------------|-----------------------------|------------------|
| RoHS Compliance Status | Compliant without exemption | |
| REACH SVHC | No SVHC above 0.1 wt% | |
| Product Carbon Footprint | Cradle to gate | 0.033 kg CO2 eq. |

General data

| | | |
|--|---|-----------|
| Adhesive | Double-sided adhesive tape | |
| Material colour according to resistance code | 4 | |
| Version | Self-adhesive | |
| Width | 60 mm | |
| UL 94 flammability rating | V-2 | |
| Operating temperature range, max. | 60 °C | |
| Operating temperature range, min. | -40 °C | |
| Colour | yellow | |
| Halogen | No | |
| Basic material | Polyamide 66 | |
| Printed characters | without | |
| Number of markers per packaging unit | Form of supply | MultiCard |
| Recommended industries | Machinery | |
| compatible printer | PRINTJET CONNECT , MCP BASIC 2 , MCP PLUS 2 | |
| Number of markers per combination | 1 MultiCard = Device markers | |
| Operating temperature range | -40...60 °C | |


Device markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001288 | ETIM 9.0 | EC001288 |
| ETIM 10.0 | EC001288 | ECLASS 14.0 | 27-28-11-04 |
| ECLASS 15.0 | 27-28-11-04 | | |

Drawings



CC 30/60 K MC NE GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Accessories



General ordering data

| | | | |
|------------|----------------------------|--|--|
| Type | ETO CC 30/60 TRANSPAR. | Version | |
| Order No. | 1934440000 | ClipCard, Accessories, 30 x 60 mm, Transparent | |
| GTIN (EAN) | 4032248590971 | | |
| Qty. | 10 ST | | |