


WSH 18 MT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

General ordering data

Version	Accessories, Rail support, metal
Order No.	1083100000
Type	WSH 18 MT
GTIN (EAN)	4008190053246
Qty.	10 items

WSH 18 MT

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Width	13.5 mm	Width (inches)	0.5315 inch
Net weight	173.51 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., max.	85 °C		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	metal	Colour	grey
UL 94 flammability rating	None		

System specifications

Version	For the mounting rails	Mounting rail	TS 35
---------	------------------------	---------------	-------

Additional technical data

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No	Type of mounting	when screwed in

Dimensions

Pitch in mm (P)	8.00 mm
-----------------	---------

General

Number of poles	1	Installation advice	Direct mounting
Mounting rail	TS 35		

Classifications

ETIM 8.0	EC001166	ETIM 9.0	EC001166
ETIM 10.0	EC001166	ECLASS 14.0	27-40-06-07
ECLASS 15.0	27-40-06-07		

Busbars



With our bus bars in various materials and the associated accessories, you can connect cables in the smallest installation space. Depending on the application, potentials can be collected, distributed or dissipated.

General ordering data

Type	SA 3.00X10.00X1000 CUZN...	Version
Order No.	0259800000	Busbar (terminal), silver, Height: 1000 mm, Depth: 3 mm, Brass
GTIN (EAN)	4008190049300	
Qty.	1 M	
Type	SSCH 10X3X1000 CU/SN	Version
Order No.	0348900000	Busbar (terminal), silver, Height: 1000 mm, Depth: 3 mm, Copper
GTIN (EAN)	4008190024802	
Qty.	25 M	
Type	SSCH 15X6X1000 CU/SN	Version
Order No.	0357400000	Busbar (terminal), silver, Height: 1000 mm, Depth: 6 mm, Copper
GTIN (EAN)	4008190169572	
Qty.	1 M	
Type	SSCH 10X3X1000 ST/ZN	Version
Order No.	0438000000	Busbar (terminal), silver, Height: 1000 mm, Depth: 3 mm, Steel
GTIN (EAN)	4008190080938	
Qty.	25 M	
Type	SSCH 6X6X1000 CU/SN	Version
Order No.	0571300000	Busbar (terminal), silver, Height: 1000 mm, Depth: 6 mm, Copper
GTIN (EAN)	4008190015039	
Qty.	1 M	
Type	SSCH 7.3X1.2X1000	Version
Order No.	1071200000	Busbar (terminal), silver, Height: 1000 mm, Depth: 1.2 mm, Copper
GTIN (EAN)	4008190279172	
Qty.	1 M	
Type	NSCH 1M	Version
Order No.	0280200000	Busbar (terminal), Natural, Height: 15 mm, Depth: 2 mm, Copper
GTIN (EAN)	4008190012953	
Qty.	10 M	
Type	ESCH 1 M	Version
Order No.	0280300000	Busbar (terminal), silver, Height: 12 mm, Depth: 2 mm, Steel
GTIN (EAN)	4008190143053	
Qty.	10 M	