

## THM ET S7 50/25 GE

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



THM ET S7 non-adhesive, roll-packaged labels are used to label the SIMATIC ET 200S and S7-modules from Siemens.

The M-Print® PRO software can be used to individually print the THM ET S7 labels with a THM printer. Labels can be easily separated. The THM MultiMark printer ensures highly-resistant printing.

### General ordering data

Version	THM, Device markers, 50 x 25 mm, Siemens, yellow
Order No.	<a href="#">1095590000</a>
Type	THM ET S7 50/25 GE
GTIN (EAN)	4032248868100
Qty.	1 ROL

## THM ET S7 50/25 GE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	0.08 mm	Depth (inches)	0.0031 inch
Height	50 mm	Height (inches)	1.9685 inch
Width	25 mm	Width (inches)	0.9842 inch
Net weight	739.2 g		

### Temperatures

Operating temperature range	-50...100 °C
-----------------------------	--------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### General data

Material colour according to resistance code	4	
Printing method	Thermal transfer	
Version	halogen-free	
Width	25 mm	
UL 94 flammability rating	HB	
Operating temperature range, max.	100 °C	
Operating temperature range, min.	-50 °C	
Colour	yellow	
Halogen	No	
Basic material	Polypropylene	
Printed characters	without	
Number of markers per packaging unit	Form of supply	Label reel
Approval acc. to UL 969	No	
compatible printer	<a href="#">THM MULTIMARK</a> , <a href="#">THM MULTIMARK PLUS</a>	
Number of markers per combination	1 Label reel = Device markers	
Operating temperature range	-50...100 °C	
Application/manufacturer	Siemens	
Number per roll	1250	

### Device markers

Halogen	No
---------	----

### Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		



## THM ET S7 50/25 GE

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

### General ordering data

Type	RIBBON MM 110/360 SW	Version	
Order No.	<a href="#">2005070000</a>	Ink ribbon	
GTIN (EAN)	4050118390049		
Qty.	1 ST		