

## IE-BIC-HYB-P-0,5-300

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Hybrid, 10-pole. Inserts for plug-in connectors Variant 14

### General ordering data

Version	Crimp contact, for flange insert, Hybrid
Order No.	<a href="#">1096150000</a>
Type	IE-BIC-HYB-P-0,5-300
GTIN (EAN)	4032248869114
Qty.	300 items

## IE-BIC-HYB-P-0,5-300

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Net weight	0.29 g
------------	--------

### Temperatures

Storage temperature	Operating temperature
Installation temperature	

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### General data

Wire cross-section, finely stranded, max. AWG 20 (AWG)	Wire cross-section, finely stranded, min. AWG 24 (AWG)
Shielding	unshielded
Wire connection cross section, finely stranded, max.	0.5 mm <sup>2</sup>
Connection 2	Crimp
Category	Miscellaneous
Wire connection cross section, finely stranded, min.	0.2 mm <sup>2</sup>

### Electrical properties

Nominal voltage	24 V
-----------------	------


### Important note

Product information	Hybrid, 10-pole. Inserts for plug-in connectors Variant 14
---------------------	--

### Classifications

ETIM 8.0	EC001121	ETIM 9.0	EC001121
ETIM 10.0	EC001121	ECLASS 14.0	27-44-03-90
ECLASS 15.0	27-44-03-90		

**Dimensioned drawing**



## IE-BIC-HYB-P-0,5-300

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### Crimping tools



Crimping tools for Weidmüller contacts for RSV and DSTV-HD systems

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With end stop for exact positioning of the contacts

### General ordering data

Type	HTF HYB	Version	
Order No.	<a href="#">1119580000</a>	Pressing tool, Crimping tool for contacts, 0.08mm <sup>2</sup> , 1mm <sup>2</sup> ,	
GTIN (EAN)	4032248900626	FoderBcrimp	
Qty.	1 ST		