

## CC 85/54 MC NE GR


**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



ClipCard device markers in MultiCard format are used for labelling electrical installations and switchgear systems, and offer an interesting alternative to engraving. Thanks to the proven MultiCard format, labelling is possible with PrintJet CONNECT or Plotter.

- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- Universal fixing
- Carrier (screwable or with cable ties)
- Tag rail (self-adhesive or screw fixing)
- Or self-adhesive tags

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

Version	ClipCard, Device markers, 54 x 85 mm, Holder Logimark-H, grey
Order No.	<a href="#">1138420000</a>
Type	CC 85/54 MC NE GR
GTIN (EAN)	4032248919864
Qty.	10 items

## CC 85/54 MC NE GR

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	0.8 mm	Depth (inches)	0.0315 inch
Height	54 mm	Height (inches)	2.126 inch
Width	85 mm	Width (inches)	3.3464 inch
Net weight	12 g		

## Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption	
REACH SVHC	No SVHC above 0.1 wt%	
Product Carbon Footprint	Cradle to gate	0.040 kg CO2 eq.

## General data

Material colour according to resistance code	8	
Version	pluggable	
Width	85 mm	
UL 94 flammability rating	V-2	
Operating temperature range, max.	100 °C	
Operating temperature range, min.	-40 °C	
Colour	grey	
Halogen	No	
Basic material	Polyamide 66	
Printed characters	without	
Number of markers per packaging unit	Form of supply	MultiCard
Recommended industries compatible printer	Machinery <a href="#">PRINTJET CONNECT</a> , <a href="#">MCP BASIC 2</a> , <a href="#">MCP PLUS 2</a>	
Number of markers per combination	1 MultiCard = Device markers	
Operating temperature range	-40...100 °C	
Application/manufacturer	Holder Logimark-H	

## Device markers

Halogen	No
---------	----

## Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		



## CC 85/54 MC NE GR

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

## Accessories

www.weidmueller.com

### Accessories



### General ordering data

Type	CC-H 85/54 SW	Version
Order No.	<a href="#">1631640001</a>	ClipCard, Accessories, 90 x 58 mm, black
GTIN (EAN)	4008190465254	
Qty.	20 ST	
Type	CC-H 85/54 GR	Version
Order No.	<a href="#">1631640002</a>	ClipCard, Accessories, 90 x 58 mm, grey
GTIN (EAN)	4008190465261	
Qty.	20 ST	
Type	CC-H 85/54 BG	Version
Order No.	<a href="#">1631640003</a>	ClipCard, Accessories, 90 x 58 mm, dark beige
GTIN (EAN)	4008190465292	
Qty.	20 ST	
Type	CC-HO 85/54 SW	Version
Order No.	<a href="#">1603290000</a>	ClipCard, Accessories, 90 x 58 mm, black
GTIN (EAN)	4008190188306	
Qty.	20 ST	