

**ZQV 1.5N/R6.4/10 GE**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**



**General ordering data**

Version	TERMSERIES, Cross-connector
Order No.	<a href="#">1193680000</a>
Type	ZQV 1.5N/R6.4/10 GE
GTIN (EAN)	4032248976454
Qty.	10 items
Delivery status	Discontinued
Available until	2021-06-30T00:00:00+02:00
Alternative product	<a href="#">TCC 6.4/10 OR</a>

**ZQV 1.5N/R6.4/10 GE**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	4.9 mm	Depth (inches)	0.1929 inch
Height	13.1 mm	Height (inches)	0.5157 inch
Width	61 mm	Width (inches)	2.4016 inch
Net weight	3.54 g		

**Temperatures**

Storage temperature -40 °C...85 °C      Operating temperature -40 °C...60 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**Rated data UL**

Rated current (UL) 10 A

**General data**

Version can be cut to length      Colour yellow

**Insulation coordination**

Rated voltage 250 V

**Connection data**

Pitch in mm (P) 6.40 mm

**Classifications**

ETIM 8.0	EC002586	ETIM 9.0	EC002586
ETIM 10.0	EC002586	ECLASS 14.0	27-37-16-92
ECLASS 15.0	27-37-16-92		


**ZQV 1.5N/R6.4/10 GE**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

**Dimensional drawing**



## ZQV 1.5N/R6.4/10 GE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Cutting tools



Cutting tools for conductors up to 8 mm, 12 mm, 14 mm and 22 mm outside diameter. The special blade geometry allows pinch-free cutting of copper and aluminium conductors with minimum physical effort. The cutting tools (KT 8 to KT 22) also come with VDE and GS-tested protective insulation up to 1,000 V in accordance with EN/IEC 60900.

#### General ordering data

Type	KT 14	Version	
Order No.	<a href="#">1157820000</a>	Cutting tools, Cutting tool for one-hand operation	
GTIN (EAN)	4032248945344		
Qty.	1 ST		

### Cutting and notching tools for cross-connections



- for Weidmüller Z-Series cross-connections
- for cross-connections from WQV 2.5 to WQV 35
- for cross-connection window of the terminal WSI 6

#### General ordering data

Type	KT ZQV	Version	
Order No.	<a href="#">9002170000</a>	Cutting tool for one-hand operation	
GTIN (EAN)	4032248291670		
Qty.	1 ST		
Type	WAW 1 NEUTRAL	Version	
Order No.	<a href="#">9004500000</a>	Miscellaneous tools	
GTIN (EAN)	4008190053925		
Qty.	1 ST		