

**DOHA KTB A5 S2 R**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com



Integrate, expand and customise - the perfect supplement to every application

The fully structured range of system accessories for the new Klippon® TB enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

Document holders

Document holders for the proper storage of documents in the enclosure

**General ordering data**

|            |  |
|------------|--|
| Version    | Klippon TB (Terminal Box), Document holders, Riveted, Height: 150 mm, Width: 180 mm, Depth: 20 mm, Basic material: Stainless steel 1.4301, Stainless steel 1.4301 (304), Mirror polished, silver |
| Order No.  | <a href="#">1252750000</a>   |
| Type       | DOHA KTB A5 S2 R   |
| GTIN (EAN) | 4050118045390  |
| Qty.       | 1 items  |

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|                             |        |                 |             |
|-----------------------------|--------|-----------------|-------------|
| Depth                       | 20 mm  | Depth (inches)  | 0.7874 inch |
| Height                      | 150 mm | Height (inches) | 5.9055 inch |
| Width                       | 180 mm | Width (inches)  | 7.0866 inch |
| Mounting dimension - height | 100 mm | Net weight      | 289 g       |

### Temperatures

Operating temperature

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

### General information

|                    |  |                      |                 |
|--------------------|--|----------------------|-----------------|
| Material thickness | 1 mm   | Surface finish       | Mirror polished |
| Basic material     | Stainless steel 1.4301,<br>Stainless steel 1.4301<br>(304) | Enclosure attachment | Fixing lugs     |

### General information on accessories

|                    |  |                             |                 |
|--------------------|--|-----------------------------|-----------------|
| Material thickness | 1 mm   | Surface finish              | Mirror polished |
| Basic material     | Stainless steel 1.4301,<br>Stainless steel 1.4301<br>(304) | Mounting dimension - height | 100 mm          |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000317    | ETIM 9.0    | EC000317    |
| ETIM 10.0   | EC000317    | ECLASS 14.0 | 27-18-28-90 |
| ECLASS 15.0 | 27-18-28-90 |             |             |