

CA 100 C**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Orders on request only



- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

General ordering data

Version	Automatic stripper and crimper
Order No.	1266370000
Type	CA 100 C
GTIN (EAN)	4050118056303
Qty.	1 items

CA 100 C

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	280 mm	Depth (inches)	11.0236 inch
Height	390 mm	Height (inches)	15.3543 inch
Width	410 mm	Width (inches)	16.1417 inch
Net weight	23000 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1

PW65 maintenance - automatic stripping/crimping

Stripping range	0.14 - 0.34 mm ² (~AWG 26 - 22)	Drive	Electropneumatic
Pulse time	approx. 1.5 s	Wire end ferrules cross-section, max.	0.34 mm ²
Wire end ferrules cross-section, min.	0.14 mm ²	Crimping length	6/8 mm
Consumables	loose cable lugs, With and without plastic collar	Length of wire-end ferrule	10/12 mm
Compressed-air connection	5 bar	Electrical connection	100-240 V / 50/65 Hz

Classifications

ETIM 8.0	EC002778	ETIM 9.0	EC002778
ETIM 10.0	EC002778	ECLASS 14.0	17-13-01-01
ECLASS 15.0	17-13-01-01		

Drawings



CA 100 C

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Accessories / replacement parts



- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

General ordering data

Type	AIMESA CF U/L/LS SK TIN	Version
Order No.	1283530000	Automatic machines, Replacement part
GTIN (EAN)	4050118073676	
Qty.	1 ST	
Type	HUEHABA 0.14 CA 100 C	Version
Order No.	1314530000	Accessories, Replacement part
GTIN (EAN)	4050118117592	
Qty.	1 ST	
Type	HUEHABA 0.25 CA 100 C	Version
Order No.	1314520000	Accessories, Replacement part
GTIN (EAN)	4050118117585	
Qty.	1 ST	
Type	HUEHABA 0.34 CA 100 C	Version
Order No.	1314510000	Accessories, Replacement part
GTIN (EAN)	4050118117370	
Qty.	1 ST	