


BZT PRV16 BL 35X15

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

General ordering data

| | |
|------------|---|
| Version | P-series, Marker holder, blue, Number of levels: 16, TS 35 x 15 |
| Order No. | 1267930000 |
| Type | BZT PRV16 BL 35X15 |
| GTIN (EAN) | 4032248112562 |
| Qty. | 20 items |

BZT PRV16 BL 35X15

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|----------|-----------------|-------------|
| Depth | 113.4 mm | Depth (inches) | 4.4646 inch |
| Height | 225 mm | Height (inches) | 8.8582 inch |
| Width | 10.2 mm | Width (inches) | 0.4016 inch |
| Net weight | 53.35 g | | |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|---------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -5 °C...40 °C |
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 125 °C |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Material data

| | | | |
|---------------------------|---------------|--------|------|
| Basic material | Polycarbonate | Colour | blue |
| UL 94 flammability rating | V-0 | | |

System specifications

| | | | |
|-------------------------------------|------------------------|------------------|------------|
| Version | For the mounting rails | Number of levels | 16 |
| Number of clamping points per level | 2 | Mounting rail | TS 35 x 15 |

Conductors for clamping (rated connection)

| | |
|-----------------------|----|
| Number of connections | 32 |
|-----------------------|----|

General

| | |
|---------------|------------|
| Mounting rail | TS 35 x 15 |
|---------------|------------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002848 | ETIM 9.0 | EC002848 |
| ETIM 10.0 | EC002848 | ECLASS 14.0 | 27-14-11-92 |
| ECLASS 15.0 | 27-14-11-92 | | |