

## CC 15/17 K MC NE RT

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration



ClipCard device markers in MultiCard format are used for labelling electrical installations and switchgear systems, and offer an interesting alternative to engraving. Thanks to the proven MultiCard format, labelling is possible with PrintJet CONNECT or Plotter.

- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- Universal fixing
- Carrier (screwable or with cable ties)
- Tag rail (self-adhesive or screw fixing)
- Or self-adhesive tags

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

Version	ClipCard, Device markers, 15 x 17 mm, red
Order No.	<a href="#">1288320000</a>
Type	CC 15/17 K MC NE RT
GTIN (EAN)	4050118079753
Qty.	80 items

## CC 15/17 K MC NE RT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	1 mm	Depth (inches)	0.0394 inch
Height	15 mm	Height (inches)	0.5906 inch
Width	17 mm	Width (inches)	0.6693 inch
Net weight	1.26 g		

### Temperatures

Operating temperature range	-40...60 °C
-----------------------------	-------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption	
REACH SVHC	No SVHC above 0.1 wt%	
Product Carbon Footprint	Cradle to gate	0.008 kg CO2 eq.

### General data

Adhesive	Double-sided adhesive tape	
Material colour according to resistance code	2	
Version	Self-adhesive	
Width	17 mm	
UL 94 flammability rating	V-2	
Operating temperature range, max.	60 °C	
Operating temperature range, min.	-40 °C	
Colour	red	
Halogen	No	
Basic material	Polyamide 66	
Printed characters	without	
Number of markers per packaging unit	Form of supply	MultiCard
Recommended industries	Machinery	
compatible printer	<a href="#">PRINTJET CONNECT</a> , <a href="#">MCP BASIC 2</a> , <a href="#">MCP PLUS 2</a>	
Number of markers per combination	1 MultiCard = Device markers	
Operating temperature range	-40...60 °C	

### Device markers

Halogen	No
---------	----

### Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		



**CC 15/17 K MC NE RT**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Accessories**

**Accessories**



**General ordering data**

Type	ETO CC 15/17 TRANSPAR.	Version	
Order No.	<a href="#">1880850000</a>	ClipCard, Accessories, 15 x 17 mm, Transparent	
GTIN (EAN)	4032248481224		
Qty.	10 ST		