

TPSDHA KTB 70X70M3 S2 R

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Nameplate holders

There are a variety of designed label holders available for prominent display as required and for additional nameplates as needed.

General ordering data

| | |
|------------|--|
| Version | Klippon TB (Terminal Box), Ratings plate holder, Riveted, Height: 70 mm, Width: 70 mm, Depth: 20 mm, Basic material: Stainless steel 1.4301, Stainless steel 1.4301 (304), Mirror polished, silver |
| Order No. | 1279320000 |
| Type | TPSDHA KTB 70X70M3 S2 R |
| GTIN (EAN) | 4050118070101 |
| Qty. | 1 items |

TPSDHA KTB 70X70M3 S2 R

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|-------|-----------------|-------------|
| Depth | 20 mm | Depth (inches) | 0.7874 inch |
| Height | 70 mm | Height (inches) | 2.7559 inch |
| Width | 70 mm | Width (inches) | 2.7559 inch |
| Net weight | 48 g | | |

Temperatures

| | |
|-----------------------|--|
| Operating temperature | |
|-----------------------|--|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General information

| | | | |
|--------------------|--|------------------------|---|
| Material thickness | 1 mm | Surface finish | Mirror polished |
| Basic material | Stainless steel 1.4301, Stainless steel 1.4301 (304) | Note: protection class | The attachment is done outside the sealed area of the housing. The angle bracket is provided with two 3.3 mm diameter holes. The holes in the housing are to be made by the customer. The attachment can be done using 3.3 mm rivets or M3 screws. The respective ratings plate is fastened to the angle bracket with M3 nuts. We recommend using M3 self-locking nuts. |

General information on accessories

| | | | |
|--------------------|--|----------------|-----------------|
| Material thickness | 1 mm | Surface finish | Mirror polished |
| Basic material | Stainless steel 1.4301, Stainless steel 1.4301 (304) | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002626 | ETIM 9.0 | EC002626 |
| ETIM 10.0 | EC002626 | ECLASS 14.0 | 27-18-28-16 |
| ECLASS 15.0 | 27-18-28-16 | | |