


**NSCH 2M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Product image**

With our bus bars in various materials and the associated accessories, you can connect cables in the smallest installation space. Depending on the application, potentials can be collected, distributed or dissipated.

**General ordering data**

Version	Busbar (terminal), brown-red, Height: 15 mm, Depth: 2 mm, Copper
Order No.	<a href="#">1313600000</a>
Type	NSCH 2M
GTIN (EAN)	4008190052096
Qty.	20 M

## NSCH 2M

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

RoHS	Conform
------	---------

## Dimensions and weights

Depth	2 mm	Depth (inches)	0.0787 inch
Height	15 mm	Height (inches)	0.5906 inch
Width	2000 mm	Width (inches)	78.74 inch
Net weight	227.5 g		

## Temperatures

Ambient temperature	-5 °C...40 °C
---------------------	---------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Material data

Basic material	Copper	Surface finish	electropolished
Colour	brown-red		

## Additional technical data

Installation advice	Direct mounting
---------------------	-----------------

## General

Installation advice	Direct mounting	Surface finish	electropolished
---------------------	-----------------	----------------	-----------------

## Rating data

Nominal current	24 A
-----------------	------

## Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-14-11-92
ECLASS 15.0	27-14-11-92		

## NSCH 2M

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Mounting support



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

## General ordering data

Type	BFSC M5X8 SCHLITZ	Version
Order No.	<a href="#">029670000</a>	Mounting screw (Terminal), 5.00 mm, Steel, Depth: 8.5 mm, Width: 8.5 mm, Height: 8.5 mm
GTIN (EAN)	4008190881764	
Qty.	100 ST	
Type	DKSUE NSCH/ESCH	Version
Order No.	<a href="#">028010000</a>	Fastening element (Terminal), silver, Height: 12.5 mm, Width: 10 mm, Steel, 180 °C
GTIN (EAN)	4008190036348	
Qty.	100 ST	

## Accessories



The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

## General ordering data

Type	SH 1	Version
Order No.	<a href="#">029986000</a>	Busbar support, beige, 100 °C, Width: 26 mm, V-2, Polyamide 66, when screwed in
GTIN (EAN)	4008190135133	
Qty.	20 ST	