

THM ESO 7 PA WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Version	Terminal markers, Insert markers, 30 x 6.3 mm, white
Order No.	1339570000
Type	THM ESO 7 PA WS
GTIN (EAN)	4050118144208
Qty.	1 items

THM ESO 7 PA WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Height	30 mm	Height (inches)	1.1811 inch
Width	6.3 mm	Width (inches)	0.248 inch
Net weight	287.76 g		

Temperatures

Operating temperature range -40...70 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Orientation of print	horizontal and vertical		
Width	6.3 mm		
Operating temperature range, max.	70 °C		
Operating temperature range, min.	-40 °C		
Colour	white		
Halogen	No		
Basic material	Paper		
Printed characters	without		
Number of markers per packaging unit	2500		
Number of markers per packaging unit	Form of supply	Label reel	
	Number of combinations per packaging unit	1	
	Number of markers per combination	2500	
Size of labelling field	30 x 6.3 mm		
Number of markers per combination	1 Label reel = 2500 Insert markers		
Operating temperature range	-40...70 °C		
Number per roll	2500		

Classifications

ETIM 8.0	EC000761	ETIM 9.0	EC000761
ETIM 10.0	EC000761	ECLASS 14.0	27-28-11-01
ECLASS 15.0	27-28-11-01		

Drawings



THM ESO 7 PA WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

WKM for inlay tags



The halogen-free, transparent pocket of the WKM offers outstanding protection against environmental influences. Thanks to firm fixation with cable ties, it is suitable for almost all wire cross-sections.

The pre-printed tags are simply inserted into the WKM holder and secured with a clip. WKM cable markers are the right solution for maximum efficiency in on-site marking. Your advantage when using WKM cables

- Paper and polyester labels can be printed individually with conventional office printers
- The robust design in combination with MultiCard ELS tags guarantees maximum protection against environmental influences

General ordering data

Type	WKM 8/30	Version	
Order No.	1631910000	WKM, Conductor and cable markers, 7 - 115 mm, 30 x 8 mm, Wire	
GTIN (EAN)	4008190206666	and cable markers, Transparent	
Qty.	50 ST		

Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM 110/360 SW	Version	
Order No.	2005070000	Ink ribbon	
GTIN (EAN)	4050118390049		
Qty.	1 ST		