

## THM MT30X DIA 30 WS

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



The THM labels offer brilliant printing quality thanks to the thermal transfer technology. Different materials and the user-friendly printing system under Windows optimise every marking effort.

- High-quality polyester labels in various colours or inexpensive paper labels are available
- Labels are automatically positioned in the printer for perfectly centred prints on each label.

### General ordering data

Version	THM, Device markers, white
Order No.	<a href="#">1339670000</a>
Type	THM MT30X DIA 30 WS
GTIN (EAN)	4050118144338
Qty.	1 items

**THM MT30X DIA 30 WS**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	0.08 mm	Depth (inches)	0.0031 inch
Diameter	30 mm	Net weight	161 g

**Temperatures**

Operating temperature range -40...150 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General data**

Adhesive	Acrylate adhesive		
Material colour according to resistance code	9		
Printing method	Thermal transfer		
Version	Self-adhesive, halogen-free		
UL 94 flammability rating	V-0		
Operating temperature range, max.	150 °C		
Operating temperature range, min.	-40 °C		
Colour	white		
Halogen	No		
Basic material	Polyester		
Printed characters	without		
Number of markers per packaging unit	Form of supply	Label reel	
Approval acc. to UL 969	Yes		
compatible printer	<a href="#">THM MULTIMARK</a> , <a href="#">THM MULTIMARK PLUS</a>		
Number of markers per combination	1 Label reel = Device markers		
Operating temperature range	-40...150 °C		
Number per roll	1000		

**Device markers**

Diameter	30 mm	Halogen	No
----------	-------	---------	----

**Classifications**

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

**THM MT30X DIA 30 WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



## THM MT30X DIA 30 WS

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Accessories

## Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

## General ordering data

Type	RIBBON MM 110/360 SW	Version	
Order No.	<a href="#">2005070000</a>	Ink ribbon	
GTIN (EAN)	4050118390049		
Qty.	1 ST		