

**TW PRV8 H-A I-R**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

**General ordering data**

|            |  |
|------------|--|
| Version    | P-series, Partition plate, grey, 2 mm, printed |
| Order No.  | <a href="#">1399770000</a>                     |
| Type       | TW PRV8 H-A I-R                                |
| GTIN (EAN) | 4050118230994                                  |
| Qty.       | 10 items                                       |

**TW PRV8 H-A I-R**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 59.7 mm | Depth (inches)  | 2.3504 inch |
| Height     | 120 mm  | Height (inches) | 4.7244 inch |
| Width      | 2 mm    | Width (inches)  | 0.0787 inch |
| Net weight | 9.5 g   |                 |             |

**Temperatures**

|                                  |                |                                  |               |
|----------------------------------|----------------|----------------------------------|---------------|
| Storage temperature              | -25 °C...55 °C | Ambient temperature              | -5 °C...40 °C |
| Continuous operating temp., min. | -50 °C         | Continuous operating temp., max. | 125 °C        |

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

**Material data**

|                           |               |        |      |
|---------------------------|---------------|--------|------|
| Basic material            | Polycarbonate | Colour | grey |
| UL 94 flammability rating | V-0           |        |      |

**System specifications**

|         |         |                  |   |
|---------|---------|------------------|---|
| Version | printed | Number of levels | 8 |
|---------|---------|------------------|---|

**Additional technical data**

Snap-on Yes

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000886    | ETIM 9.0    | EC000886    |
| ETIM 10.0   | EC000886    | ECLASS 14.0 | 27-25-03-01 |
| ECLASS 15.0 | 27-25-03-01 |             |             |