

THM UR20 GE**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



THM ET S7 non-adhesive, roll-packaged labels are used to label the SIMATIC ET 200S and S7-modules from Siemens.

The M-Print® PRO software can be used to individually print the THM ET S7 labels with a THM printer. Labels can be easily separated. The THM MultiMark printer ensures highly-resistant printing.

General ordering data

Version	THM, Insert markers, 90 x 8 mm, yellow
Order No.	1429910000
Type	THM UR20 GE
GTIN (EAN)	4050118234787
Qty.	1 items
Delivery status	Discontinued
Available until	2025-12-10T00:00:00+01:00

THM UR20 GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0.08 mm	Depth (inches)	0.0031 inch
Height	90 mm	Height (inches)	3.5433 inch
Width	8 mm	Width (inches)	0.315 inch
Net weight	287.76 g		

Temperatures

Operating temperature range	-40...80 °C
-----------------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Number per sheet	1000
Printing method	Thermal transfer
Version	Self-adhesive
Width	8 mm
UL 94 flammability rating	HB
Operating temperature range, max.	80 °C
Operating temperature range, min.	-40 °C
Colour	yellow
Halogen	Yes
Basic material	Vinyl film
Printed characters	without
Number of markers per packaging unit	Form of supply
Approval acc. to UL 969	No
compatible printer	THM MULTIMARK , THM MULTIMARK PLUS
Number of markers per combination	1 Label reel = Insert markers
Operating temperature range	-40...80 °C
Number per roll	1000

Device markers

Halogen	Yes
---------	-----

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

Drawings



Accessories**Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM 110/360 SW	Version	
Order No.	2005070000	Ink ribbon	
GTIN (EAN)	4050118390049		
Qty.	1 ST		