

SCREWTY-SW13-DM**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The ideal tool for any application

Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

General ordering data

Version	Bolting tool
Order No.	1389190000
Type	SCREWTY-SW13-DM
GTIN (EAN)	4050118189742
Qty.	1 items
Packaging	Cardboard box

SCREWTY-SW13-DM

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	226.26 g
------------	----------

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

Screwing tools

Torque setting, max.	1.7 Nm	Torque setting, min.	0.5 Nm
----------------------	--------	----------------------	--------

Important note

Product information	Included in delivery: <ul style="list-style-type: none">• Torque screwdriver 0.5-1.7 Nm + Setting aid• Interchangeable blade AF13
---------------------	--

Classifications

ETIM 6.0	EC000149	ETIM 7.0	EC000149
ETIM 8.0	EC000149	ETIM 9.0	EC000149
ETIM 10.0	EC000149	ECLASS 9.0	21-04-50-03
ECLASS 9.1	21-01-90-90	ECLASS 10.0	21-04-50-03
ECLASS 11.0	21-01-90-90	ECLASS 12.0	21-01-90-90
ECLASS 13.0	21-01-90-90	ECLASS 14.0	21-01-90-90
ECLASS 15.0	21-01-90-90		

SCREWTY-SW13-DM

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Screwty® cable gland tool with torque function



The ideal tool for any application

Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

General ordering data

Type	SCREWTY SW9	Version
Order No.	1254630000	Interchangeable blade for cable gland tool
GTIN (EAN)	4050118054194	
Qty.	1 ST	
Type	SCREWTY SW10	Version
Order No.	1254640000	Interchangeable blade for cable gland tool
GTIN (EAN)	4050118048599	
Qty.	1 ST	
Type	SCREWTY SW12	Version
Order No.	2598970000	Interchangeable blade for cable gland tool
GTIN (EAN)	4050118781151	
Qty.	1 ST	
Type	SCREWTY SW13	Version
Order No.	1254650000	Interchangeable blade for cable gland tool
GTIN (EAN)	4050118051834	
Qty.	1 ST	
Type	SCREWTY SW15	Version
Order No.	1290830000	Interchangeable blade for cable gland tool
GTIN (EAN)	4050118084320	
Qty.	1 ST	
Type	SCREWTY SW17	Version
Order No.	1254660000	Interchangeable blade for cable gland tool
GTIN (EAN)	4050118051841	
Qty.	1 ST	
Type	SCREWTY SW18	Version
Order No.	1254670000	Interchangeable blade for cable gland tool
GTIN (EAN)	4050118051858	
Qty.	1 ST	
Type	SCREWTY SW19	Version
Order No.	1254680000	Interchangeable blade for cable gland tool
GTIN (EAN)	4050118048827	
Qty.	1 ST	