

**IE-FC-IP-1ST/1D9/1D25****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



FrontCom® Vario integrates multiple functions in only one single frame. The system is easy to install and you can select from a wide range of data, signal and power modules. In addition to being extremely compact, FrontCom® Vario offers a number of unique product features that will make your project planning and work activities secure, fast and future-proof. Furthermore, the FrontCom® Vario system has an attractive housing design that, by the way, offers highest impact-resistance and fully meets the requirements of IP 65 protection class.

**General ordering data**

Version	FrontCom, Insert plate, unshielded
Order No.	<a href="#">1450650000</a>
Type	IE-FC-IP-1ST/1D9/1D25
GTIN (EAN)	4050118255348
Qty.	1 items

**IE-FC-IP-1ST/1D9/1D25**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate No. (cURus)	E223801

**Dimensions and weights**

Height	23 mm	Height (inches)	0.9055 inch
Width	51.5 mm	Width (inches)	2.0276 inch
Length	90.5 mm	Length (inches)	3.563 inch
Net weight	13.5 g		

**Temperatures**

Storage temperature	Operating temperature	-40 °C...70 °C
Installation temperature		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3
SCIP	8a473a8a-33d4-43 18-8088-c28f0 19e7f77

**General data**

Product type	Insert plate, unshielded	Material	Polycarbonate PC
--------------	--------------------------	----------	------------------

**Inserts**

Insert, signal, D-Sub, 25-pole	1	Insert, data	1
Signal insert D-Sub 9-pole / VGA / HDMI	1		

**General standards**

Certificate No. (cURus)	E223801	Certificate No. (DNV)	TAA000022B
Certificate No. (CSA)	2000039-80039714		

**Classifications**

ETIM 8.0	EC000456	ETIM 9.0	EC000456
ETIM 10.0	EC000456	ECLASS 14.0	27-18-28-92
ECLASS 15.0	27-18-28-92		

**Dimensioned drawing**

