

## HSS-HF 2.4-4.8 EL Y13M

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

### General ordering data

|            |   |
|------------|---|
| Version    | Conductor and cable markers, 2.4 - 4.8 mm, yellow |
| Order No.  | <a href="#">1423240000</a>                        |
| Type       | HSS-HF 2.4-4.8 EL Y13M                            |
| GTIN (EAN) | 4050118227697                                     |
| Qty.       | 1 items   |

## HSS-HF 2.4-4.8 EL Y13M

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |          |                 |             |
|------------|----------|-----------------|-------------|
| Depth      | 0.9 mm   | Depth (inches)  | 0.0354 inch |
| Width      | 7.6 mm   | Width (inches)  | 0.2992 inch |
| Length     | 13000 mm | Length (inches) | 511.81 inch |
| Net weight | 138 g    |                 |             |

### Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -55...105 °C |
|-----------------------------|--------------|

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

### General data

|                                   |              |                                   |  |
|-----------------------------------|--------------|-----------------------------------|--|
| Type of printing                  | neutral      | Width                             | 7.6 mm   |
| Operating temperature range, max. | 105 °C       | Operating temperature range, min. | -55 °C   |
| Colour                            | yellow       | Halogen                           | No   |
| Length                            | 13000 mm     | Basic material                    | Polyolefine  |
| Printed characters                | without      | compatible printer                | <a href="#">THM MULTIMARK</a> , <a href="#">THM MULTIMARK PLUS</a> |
| Operating temperature range       | -55...105 °C | Number per roll                   | 1  |

### Conductor and cable markers

|                                   |                          |                               |                   |
|-----------------------------------|--------------------------|-------------------------------|-------------------|
| Halogen                           | No                       | Conductor cross-section, max. | 4 mm <sup>2</sup> |
| Conductor cross-section, min.     | 0.75 mm <sup>2</sup>     | Conductor O.D., max.          | 4.8 mm            |
| Conductor O.D., min.              | 2.4 mm                   | Rate of shrinkage             | 2:1               |
| Recommended shrinking temperature | 90 °C                    | Text field width              | 0 mm              |
| Text field height                 | 7.4 mm                   | Conductor O.D.                | 2.4 - 4.8 mm      |
| Cross-section for connected wire  | 0.75 - 4 mm <sup>2</sup> |                               |                   |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |

**HSS-HF 2.4-4.8 EL Y13M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



## HSS-HF 2.4-4.8 EL Y13M

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

#### General ordering data

|            |                            |            |  |
|------------|----------------------------|------------|--|
| Type       | RIBBON HSS HF EL 40/300... | Version    |  |
| Order No.  | <a href="#">1426210000</a> | Ink ribbon |  |
| GTIN (EAN) | 4050118228823              |            |  |
| Qty.       | 1 ST                       |            |  |

### THM MULTIMARK



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

#### General ordering data

|            |                            |         |  |
|------------|----------------------------|---------|--|
| Type       | MULTIMARK ROLLER 115       | Version |  |
| Order No.  | <a href="#">1357420000</a> |         |  |
| GTIN (EAN) | 4050118160314              |         |  |
| Qty.       | 1 ST                       |         |  |
| Type       | MULTIMARK ROLLER 30        | Version |  |
| Order No.  | <a href="#">1357430000</a> |         |  |
| GTIN (EAN) | 4050118160253              |         |  |
| Qty.       | 1 ST                       |         |  |

### THM MULTIMARK PLUS



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

## HSS-HF 2.4-4.8 EL Y13M

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### General ordering data

|            |                            |         |
|------------|----------------------------|---------|
| Type       | MULTIMARK PLUS ROLLER 1... | Version |
| Order No.  | <a href="#">2672590000</a> |         |
| GTIN (EAN) | 4050118708097              |         |
| Qty.       | 1 ST                       |         |