

## HSS-HF 25.4-50.8EL Y10M

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

### General ordering data

Version	Conductor and cable markers, 25.4 - 50.8 mm, yellow
Order No.	<a href="#">1423320000</a>
Type	HSS-HF 25.4-50.8EL Y10M
GTIN (EAN)	4050118227659
Qty.	1 items

## HSS-HF 25.4-50.8EL Y10M

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	1.5 mm	Depth (inches)	0.0591 inch
Width	79.3 mm	Width (inches)	3.122 inch
Length	10000 mm	Length (inches)	393.7 inch
Net weight	1256 g		

## Temperatures

Operating temperature range	-55...105 °C
-----------------------------	--------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## General data

Type of printing	neutral	Width	79.3 mm
Operating temperature range, max.	105 °C	Operating temperature range, min.	-55 °C
Colour	yellow	Halogen	No
Length	10000 mm	Basic material	Polyolefine
Printed characters	without	Recommended industries	Transportation
compatible printer	<a href="#">THM MULTIMARK</a> , <a href="#">THM MULTIMARK PLUS</a>	Operating temperature range	-55...105 °C
Number per roll	1		

## Conductor and cable markers

Halogen	No	Conductor cross-section, max.	300 mm <sup>2</sup>
Conductor cross-section, min.	120 mm <sup>2</sup>	Conductor O.D., max.	50.8 mm
Conductor O.D., min.	25.4 mm	Rate of shrinkage	2:1
Recommended shrinking temperature	90 °C	Conductor O.D.	25.4 - 50.8 mm
Cross-section for connected wire	120 - 300 mm <sup>2</sup>		

## Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

**HSS-HF 25.4-50.8EL Y10M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

