

**GZ 12.5A/F****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Similar to illustration

As accessories for our wide product portfolio of fuse terminal blocks, we also offer the appropriate fuse links. The portfolio includes device protection fuses (miniature fuses) from 5x20 mm up to 10x38 mm, E 14 to E 18 fuse links, as well as automotive fuses and automatic circuit breakers. Gauge rings for the fuse holders round off the overall portfolio.

**General ordering data**

|            |  |
|------------|--|
| Version    | Miniature fuse, quick-acting, 12.5 A, G-Si. 6.3 x 32 |
| Order No.  | <a href="#">1460650000</a>                           |
| Type       | GZ 12.5A/F   |
| GTIN (EAN) | 4050118266627  |
| Qty.       | 10 items   |

## GZ 12.5A/F

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 6.3 mm | Depth (inches)  | 0.248 inch  |
| Height     | 32 mm  | Height (inches) | 1.2598 inch |
| Width      | 6.3 mm | Width (inches)  | 0.248 inch  |
| Net weight | 2.11 g |                 |             |

### Temperatures

|                     |               |
|---------------------|---------------|
| Ambient temperature | -5 °C...40 °C |
|---------------------|---------------|

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

### Material data

|        |            |
|--------|------------|
| Colour | Light Grey |
|--------|------------|

### System specifications

|         |                  |
|---------|------------------|
| Version | Fuse accessories |
|---------|------------------|

### Additional technical data

|                     |                 |                  |         |
|---------------------|-----------------|------------------|---------|
| Installation advice | Direct mounting | Type of mounting | Plugged |
|---------------------|-----------------|------------------|---------|

### General

|                     |                 |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

### Rating data

|               |       |                 |        |
|---------------|-------|-----------------|--------|
| Rated voltage | 500 V | Nominal current | 12.5 A |
|---------------|-------|-----------------|--------|

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002704    | ETIM 9.0    | EC002704    |
| ETIM 10.0   | EC002704    | ECLASS 14.0 | 27-14-20-01 |
| ECLASS 15.0 | 27-14-20-01 |             |             |