

## VFSKHI/4,0-6,0/638

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Insulated tab-connector sleeves made from PVC with copper sleeve

- Commercially available designs
- Not soldered
- With conical entry funnel

### General ordering data

|            |  |
|------------|--|
| Version    | cable lug, terminal end, Insulated cable connector, 6 mm <sup>2</sup> , 4 mm <sup>2</sup> - 6 mm <sup>2</sup> , yellow |
| Order No.  | <a href="#">1491750000</a>   |
| Type       | VFSKHI/4,0-6,0/638   |
| GTIN (EAN) | 4050118301816  |
| Qty.       | 100 items  |

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Net weight 1.8 g

**Environmental Product Compliance**


RoHS Compliance Status Compliant with exemption  
 RoHS Exemption (if applicable/known) 6c  
 REACH SVHC Lead 7439-92-1  
 SCIP 7b42d2b9-0a0f-4f66-a989-e9bfbbfeb1b3

**Connectors**

|                               |                   |                               |                                |
|-------------------------------|-------------------|-------------------------------|--------------------------------|
| Conductor cross-section, max. | 6 mm <sup>2</sup> | Conductor cross-section, min. | 4 mm <sup>2</sup>              |
| Conductor cross-section       | 6 mm <sup>2</sup> | Insulation                    | Available, Partially insulated |
| Dimension                     | 6.3 x 0.8 mm      | Material/plastic              | PVC                            |
| Length 1 (l1)                 | 23.3 mm           | Identification colour         | yellow                         |
| Plug-in width (d2)            | 6.3 mm            | Plug-in density (d3)          | 0.8 mm                         |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC0005 16   | ETIM 9.0    | EC0005 16   |
| ETIM 10.0   | EC0005 16   | ECLASS 14.0 | 27-44-03-92 |
| ECLASS 15.0 | 27-44-03-92 |             |             |



**Accessories**

**Crimping tools**



Crimping tools for insulated connectors  
 cable lugs, terminal pins, parallel and serial connectors,  
 plug-in connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.
- Tested to DIN EN 60352 part 2

**General ordering data**

|            |                            |   |
|------------|----------------------------|---|
| Type       | CTI 6                      | Version   |
| Order No.  | <a href="#">9006120000</a> | Pressing tool, Crimping tool for contacts, 0.5mm <sup>2</sup> , 6mm <sup>2</sup> , Oval     |
| GTIN (EAN) | 4008190044527              | crimping, Double crimp  |
| Qty.       | 1 ST                       |   |
| Type       | CTI 6 G                    | Version   |
| Order No.  | <a href="#">9202850000</a> | Pressing tool, Tool for insulated cable connectors, 0.5mm <sup>2</sup> , 6mm <sup>2</sup> , |
| GTIN (EAN) | 4032248517855              | Oval crimping, Parallel crimp   |
| Qty.       | 1 ST                       |   |