

SET PZ 6 ROTO L RC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Crimp sets

General ordering data

Version	Assortment crimping tool, Crimping tool: PZ 6 Roto L, Crimping range, min.: 0.5, Colour code: Weidmueller
Order No.	1470940000
Type	SET PZ 6 ROTO L RC
GTIN (EAN)	4050118278132
Qty.	1 items
Packaging	Plastic box

SET PZ 6 ROTO L RC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	261 mm	Depth (inches)	10.2756 inch
Height	57 mm	Height (inches)	2.2441 inch
Width	338 mm	Width (inches)	13.3071 inch
Net weight	1592.8 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	Lead 7439-92-1
SCIP	1eacbb3e-7931-4ebb-9179-f29fd9b50028

Assortments

Crimping range, max.	6 mm ²	Crimping range, min.	0.5 mm ²
Packaging	Plastic box	Crimping tool	PZ 6 Roto L
Colour code	Weidmueller	Number of AEH	4250 pcs.

Classifications

ETIM 8.0	EC000181	ETIM 9.0	EC000181
ETIM 10.0	EC000181	ECLASS 14.0	21-10-01-90
ECLASS 15.0	21-10-01-90		

SET PZ 6 ROTO L RC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Crimping tools



Crimping tools for wire end ferrules, with and without plastic collars

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Type	PZ 6 ROTO L	Version	
Order No.	1444050000	Pressing tool, Crimping tool for wire-end ferrules, 0.14mm ² , 6mm ² ,	
GTIN (EAN)	4050118248593	Trapezoidal crimp	
Qty.	1 ST		

packed loose in polythene bag



- supplied loose in polybag
- Weidmüller colour code
- DIN colour code

General ordering data

Type	H0,5/14 OR	Version	
Order No.	0690700000	Wire-end ferrule, Standard, 10 mm, 8 mm, orange	
GTIN (EAN)	4008190015770		
Qty.	500 ST		
Type	H0,75/14 W	Version	
Order No.	0462900000	Wire-end ferrule, Standard, 10 mm, 8 mm, white	
GTIN (EAN)	4008190033248		
Qty.	500 ST		
Type	H1,0/14 GE	Version	
Order No.	0463000000	Wire-end ferrule, Standard, 10 mm, 8 mm, yellow	
GTIN (EAN)	4008190024697		
Qty.	500 ST		
Type	H1,5/14 R	Version	
Order No.	0463100000	Wire-end ferrule, Standard, 10 mm, 8 mm, red	
GTIN (EAN)	4008190065089		
Qty.	500 ST		
Type	H2,5/15D BL	Version	
Order No.	9019160000	Wire-end ferrule, Standard, 10 mm, 8 mm, blue	
GTIN (EAN)	4008190028732		
Qty.	500 ST		

SET PZ 6 ROTO L RC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Multi-bag



- In multi-pack bag
- Weidmüller colour code
- Other colour code

General ordering data

Type	H4,0/18 GR SV	Version	
Order No.	9026010000	Wire-end ferrule, Standard, 12 mm, 10 mm, grey	
GTIN (EAN)	4008190117382		
Qty.	250 ST		

Conductor nom. cross-section 6.0mm²



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Type	H6,0/20 SW	Version	
Order No.	0533500000	Wire-end ferrule, Standard, 14 mm, 12 mm, black	
GTIN (EAN)	4008190183905		
Qty.	100 ST		

Case



- Body of case made from unbreakable polypropylene
- Portable and uncluttered storage in minimum space
- With two sturdy sliding catches
- Assortment cases and boxes can be placed upright and can be stacked safely without any sliding
- can be subdivided with inserts

General ordering data

Type	KOFFER PSC4-01	Version	
Order No.	9028860000	Tools, Assortment box	
GTIN (EAN)	4032248304608		
Qty.	1 ST		

SET PZ 6 ROTO L RC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Inserts



- Body of case made from unbreakable polypropylene
- Portable and uncluttered storage in minimum space
- With two sturdy sliding catches
- Assortment cases and boxes can be placed upright and can be stacked safely without any sliding
- can be subdivided with inserts

General ordering data

Type	EINSATZ A8-1 CL55	Version	
Order No.	9028460000	Assortment of inserts	
GTIN (EAN)	4032248310029		
Qty.	100 ST		
Type	EINSATZ A7-1 CL55	Version	
Order No.	9028450000	Assortment of inserts	
GTIN (EAN)	4032248310012		
Qty.	1 ST		