

## FSKI/4,0-6,0/638

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Insulated tab connector made from PVC with copper sleeve

- Commercially available designs
- Not soldered
- With conical entry funnel

### General ordering data

Version	cable lug, terminal end, Insulated cable connector, 6 mm <sup>2</sup> , 4 mm <sup>2</sup> - 6 mm <sup>2</sup> , yellow
Order No.	<a href="#">1491840000</a>
Type	FSKI/4,0-6,0/638
GTIN (EAN)	4050118301823
Qty.	100 items

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Net weight 1.71 g

**Environmental Product Compliance**


RoHS Compliance Status Compliant with exemption  
 RoHS Exemption (if applicable/known) 6c  
 REACH SVHC Lead 7439-92-1  
 SCIP 7b42d2b9-0a0f-4f66-a989-e9bfbbfeb1b3

**Connectors**

Conductor cross-section, max.	6 mm <sup>2</sup>	Conductor cross-section, min.	4 mm <sup>2</sup>
Conductor cross-section	6 mm <sup>2</sup>	Insulation	Available, Partially insulated
Dimension	6.3 x 0.8 mm	Material/plastic	PVC
Length 1 (l1)	24 mm	Identification colour	yellow
Plug-in width (d2)	6.3 mm	Plug-in density (d3)	0.8 mm

**Classifications**

ETIM 8.0	EC0005 16	ETIM 9.0	EC0005 16
ETIM 10.0	EC0005 16	ECLASS 14.0	27-44-03-92
ECLASS 15.0	27-44-03-92		



## Accessories

### Crimping tools



Crimping tools for insulated connectors  
 cable lugs, terminal pins, parallel and serial connectors,  
 plug-in connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.
- Tested to DIN EN 60352 part 2

### General ordering data

Type	CTI 6	Version
Order No.	<a href="#">9006120000</a>	Pressing tool, Crimping tool for contacts, 0.5mm <sup>2</sup> , 6mm <sup>2</sup> , Oval crimping, Double crimp
GTIN (EAN)	4008190044527	
Qty.	1 ST	
Type	CTI 6 G	Version
Order No.	<a href="#">9202850000</a>	Pressing tool, Tool for insulated cable connectors, 0.5mm <sup>2</sup> , 6mm <sup>2</sup> , Oval crimping, Parallel crimp
GTIN (EAN)	4032248517855	
Qty.	1 ST	