

Orders on request only



- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

General ordering data

Version	Automatic stripper and crimper
Order No.	1476920000
Type	CA 100 - 2.5
GTIN (EAN)	4050118283754
Qty.	1 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	420 mm	Depth (inches)	16.5354 inch
Height	425 mm	Height (inches)	16.7323 inch
Width	470 mm	Width (inches)	18.5039 inch
Net weight	38000 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1




PW65 maintenance - automatic stripping/crimping

Stripping range	0.34 - 4 mm ² (~AWG 22 - 12)	Drive	Electropneumatic
Pulse time	approx. 1.5 s	Crimping	Quadrocrimp
Wire end ferrules cross-section, max.	4 mm ²	Wire end ferrules cross-section, min.	0.34 mm ²
Crimping length	6/8/10/12 mm	Consumables	loose cable lugs, with plastic collar
Length of wire-end ferrule	12/14/16/18 mm	Compressed-air connection	5 bar
Electrical connection	100-240 V / 50/65 Hz		

Classifications

ETIM 8.0	EC002778	ETIM 9.0	EC002778
ETIM 10.0	EC002778	ECLASS 14.0	17-13-01-01
ECLASS 15.0	17-13-01-01		

Drawings



CA 100 - 2.5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Accessories / replacement parts



- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

General ordering data

Type	SOT 1,0 CA 100-2.5	Version
Order No.	1477050000	Automatic machines, Replacement part
GTIN (EAN)	4050118283877	
Qty.	1 ST	
Type	SOT 2,5 CA 100-2.5	Version
Order No.	1477040000	Automatic machines, Replacement part
GTIN (EAN)	4050118283860	
Qty.	1 ST	
Type	URS 0.34 CA 100-2.5	Version
Order No.	1550340000	Automatic machines, Replacement part
GTIN (EAN)	4050118357110	
Qty.	1 ST	
Type	URS 4.0 CA 100-2.5	Version
Order No.	1550250000	Automatic machines, Replacement part
GTIN (EAN)	4050118356946	
Qty.	1 ST	
Type	HUEHABA 0,75 CA 100-2.5	Version
Order No.	1476900000	Accessories, Replacement part
GTIN (EAN)	4050118283655	
Qty.	1 ST	
Type	HUEHABA 0.5 CA 100-2.5	Version
Order No.	1476850000	Accessories, Replacement part
GTIN (EAN)	4050118283709	
Qty.	1 ST	
Type	HUEHABA 1,0 CA 100-2.5	Version
Order No.	1476870000	Accessories, Replacement part
GTIN (EAN)	4050118283723	
Qty.	1 ST	
Type	HUEHABA 1,5 CA 100-2.5	Version
Order No.	1476880000	Accessories, Replacement part
GTIN (EAN)	4050118283587	
Qty.	1 ST	
Type	HUEHABA 2,5 CA 100-2.5	Version
Order No.	1476890000	Accessories, Replacement part
GTIN (EAN)	4050118283747	
Qty.	1 ST	
Type	LIFI 1.0 CA 100-2.5	Version
Order No.	1550370000	Automatic machines, Replacement part
GTIN (EAN)	4050118356878	
Qty.	1 ST	

CA 100 - 2.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Type	LIFI 2.5 CA 100-2.5	Version	
Order No.	1550350000	Automatic machines, Replacement part	
GTIN (EAN)	4050118356861		
Qty.	1 ST		
Type	AIMESA V	Version	
Order No.	9050180000	Accessories, Set of cutters	
GTIN (EAN)	4008190343378		
Qty.	1 ST		