

## DMS PRO

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

Only for Europe



Weidmüller torque screwdrivers have an ergonomic design and are therefore ideal for use with one hand. They can be used without causing fatigue in all installation positions. Apart from that, they incorporate an automatic torque limiter and have a good reproducibility accuracy.

### General ordering data

Version	Mounting tool
Order No.	<a href="#">1479120000</a>
Type	DMS PRO
GTIN (EAN)	4050118287011
Qty.	1 items

**DMS PRO**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Depth	46 mm	Depth (inches)	1.811 inch
Height	134 mm	Height (inches)	5.2756 inch
Width	276 mm	Width (inches)	10.8661 inch
Length	46 mm	Length (inches)	1.811 inch
Net weight	480 g		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant
RoHS Exemption (if applicable/known)	7a, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	8a39b146-a7e9-4fe1-a2bc-f82c0bb3aeeb

**Technical data**

Description of article	Mains-operated torque screwdriver with 1/4" drive
------------------------	---

**Electric screwdriver**

Charger output	DC 2.8...6V; 4.8A / 30W max.	Charger input	AC 220-240V~50-60Hz 30W
Idling speed	200 u. 600 min-1	Weight	500 g
Nominal voltage	3.6 V	Bit holder	1/4" DIN 3126 Form E6.3
Torque setting, max.	2.83 Nm	Torque setting, min.	0.36 Nm
Rechargeable batteries	Li-Ion battery	Battery voltage	3.6 V
Max. coupling torque	3 Nm		

**Screwing tools**

Torque setting, max.	2.83 Nm	Torque setting, min.	0.36 Nm
----------------------	---------	----------------------	---------

**Classifications**

ETIM 8.0	EC001395	ETIM 9.0	EC001395
ETIM 10.0	EC001395	ECLASS 14.0	21-05-08-90
ECLASS 15.0	21-05-08-90		


**Example of use**



**Example of use**



**Example of use**



## DMS PRO

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## BE6.3 bits - slotted

1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection  
Slot-head bits DIN 5264, 1/4" drive, E6.3 DIN 3126



## General ordering data

Type	BIT E6,3 0,5X3,0X70	Version
Order No.	<a href="#">9024000000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4008190852634	
Qty.	5 ST	
Type	BIT E6,3 0,6X3,5X70	Version
Order No.	<a href="#">9024020000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4008190852627	
Qty.	5 ST	
Type	BIT E6,3 0,8X4,0X70	Version
Order No.	<a href="#">9024030000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4008190852658	
Qty.	5 ST	
Type	BIT E6,3 1,0X5,5X70	Version
Order No.	<a href="#">9024040000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4008190852665	
Qty.	5 ST	

## E6.3 bits - Phillips / recess

1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection  
Crosshead bits are Phillips-Recessed type PH/DIN 5260.  
1/4" drive, E6.3 DIN 3126



## General ordering data

Type	BIT E6,3 PH1X70	Version
Order No.	<a href="#">9024080000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4008190870744	
Qty.	5 ST	
Type	BIT E6,3 PH2X70	Version
Order No.	<a href="#">9024090000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4008190870720	
Qty.	5 ST	

## DMS PRO

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### E6.3 bits - Pozidriv / Supadriv

1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection  
 Crosshead bits Pozidriv PZ/DIN 5262, 1/4" drive, E 6.3 DIN 3126



#### General ordering data

Type	BIT E6,3 PZ1X70	Version	
Order No.	<a href="#">9024100000</a>	Accessories, Screwdriver insert	
GTIN (EAN)	4008190870713		
Qty.	5 ST		

Type	BIT E6,3 PZ2X70	Version	
Order No.	<a href="#">9024110000</a>	Accessories, Screwdriver insert	
GTIN (EAN)	4008190870706		
Qty.	5 ST		

### BE6.3 bits - slotted

1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection  
 Slot-head bits DIN 5264, 1/4" drive, E6.3 DIN 3126



#### General ordering data

Type	BIT E6,3 Z 0.8X4.0X39	Version	
Order No.	<a href="#">9025590000</a>	Accessories, Screwdriver insert	
GTIN (EAN)	4008190151935		
Qty.	10 ST		

Type	BIT E6,3 0,4X2,5X70	Version	
Order No.	<a href="#">9202750000</a>	Accessories, Screwdriver insert	
GTIN (EAN)	4032248504725		
Qty.	5 ST		

Type	BIT E6,3 1,2X6,5X70	Version	
Order No.	<a href="#">9202740000</a>	Accessories, Screwdriver insert	
GTIN (EAN)	4032248504718		
Qty.	5 ST		

## DMS PRO

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Bit assortment, E6.3



1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection

## General ordering data

Type	BIT-BOX WI DMS 3	Version	
Order No.	<a href="#">9024970000</a>	Accessories, Mounting tool	
GTIN (EAN)	4032248068067		
Qty.	1 ST		

## DMS PRO



Weidmüller torque screwdrivers have an ergonomic design and are therefore ideal for use with one hand. They can be used without causing fatigue in all installation positions. Apart from that, they incorporate an automatic torque limiter and have a good reproducibility accuracy.

## General ordering data

Type	AKKU DMS PRO	Version	
Order No.	<a href="#">1479110000</a>	Mounting tool	
GTIN (EAN)	4050118348712		
Qty.	1 ST		

## DMS 3



Weidmüller torque screwdrivers have an ergonomic design and are therefore ideal for use with one hand. They can be used without causing fatigue in all installation positions. Apart from that, they incorporate an automatic torque limiter and have a good reproducibility accuracy.

## General ordering data

Type	LG DMS PRO/ DMS 3	Version	
Order No.	<a href="#">9007460000</a>	DMS 3, 90 % bei 3x 500 V AC / > 91 % bei 3 x 400 V AC	
GTIN (EAN)	4008190404970		
Qty.	1 ST		

## DMS PRO

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

## Accessories

[www.weidmueller.com](http://www.weidmueller.com)

### DMS PRO



Weidmüller torque screwdrivers have an ergonomic design and are therefore ideal for use with one hand. They can be used without causing fatigue in all installation positions. Apart from that, they incorporate an automatic torque limiter and have a good reproducibility accuracy.

### General ordering data

Type	DMS PRO SET	Version	
Order No.	<a href="#">1479090000</a>	Mounting tool	
GTIN (EAN)	4050118286786		
Qty.	1 ST		