

## VPLN/1,5-2,5

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Similar to illustration



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

|                 |   |
|-----------------|---|
| Version         | cable lug, terminal end, 1.5 mm <sup>2</sup> - 2.5 mm <sup>2</sup> , None |
| Order No.       | <a href="#">1492870000</a>  |
| Type            | VPLN/1,5-2,5  |
| GTIN (EAN)      | 4050118302578   |
| Qty.            | 100 items   |
| Delivery status | This article will no longer be available in the future.                   |
| Available until | 2026-03-31T00:00:00+02:00   |

**Technical data**

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Dimensions and weights**

|            |        |
|------------|--------|
| Net weight | 0.47 g |
|------------|--------|

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

**Connectors**

|                                |                     |                               |                     |
|--------------------------------|---------------------|-------------------------------|---------------------|
| Conductor cross-section, max.  | 2.5 mm <sup>2</sup> | Conductor cross-section, min. | 1.5 mm <sup>2</sup> |
| Insulation                     | not available       | Inside diameter of shaft (d1) | 2.3 mm              |
| Outside diameter of shaft (d3) | 4 mm                | Connection length (l)         | 7 mm                |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001059    | ETIM 9.0    | EC001059    |
| ETIM 10.0   | EC001059    | ECLASS 14.0 | 27-40-02-12 |
| ECLASS 15.0 | 27-40-02-12 |             |             |

Drawings



## Accessories

### Crimping tools



Crimping tools for non-insulated connectors  
Rolled cable lugs, tubular cable lugs, terminal pins,  
parallel and serial connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

### General ordering data

|            |                            |   |  |
|------------|----------------------------|---|--|
| Type       | HTN 21                     | Version   |  |
| Order No.  | <a href="#">9014610000</a> | Pressing tool, Crimping tool for contacts, 0.5mm <sup>2</sup> , 6mm <sup>2</sup> , Indent |  |
| GTIN (EAN) | 4008190152734              | crimp   |  |
| Qty.       | 1 ST                       |   |  |