

KRN-M3/-0,75**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

| | |
|-----------------|--|
| Version | cable lug, terminal end, 0.75 mm ² , 0.5 mm ² - 0.75 mm ² |
| Order No. | 1495010000 |
| Type | KRN-M3/-0,75 |
| GTIN (EAN) | 4050118304800 |
| Qty. | 100 items |
| Delivery status | This article will no longer be available in the future. |
| Available until | 2026-03-31T00:00:00+02:00 |

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | |
|------------|--------|
| Net weight | 0.73 g |
|------------|--------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Technical data

| | |
|---------|-----------------------|
| Version | Euro series, standard |
|---------|-----------------------|


Connectors

| | | | |
|--------------------------------|----------------------|--------------------------------|---------------------|
| Conductor cross-section, max. | 0.75 mm ² | Conductor cross-section, min. | 0.5 mm ² |
| Conductor cross-section | 0.75 mm ² | Insulation | not available |
| Hole | M 3 | Identification colour | None |
| Inside diameter of shaft (d1) | 1.4 mm | Outside diameter of shaft (d3) | 3 mm |
| Shaft length (a) | 6 mm | Connection length (l) | 12.5 mm |
| Inside diameter of flange (d2) | 3.2 mm | Flange width (b) | 6.5 mm |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001051 | ETIM 9.0 | EC001051 |
| ETIM 10.0 | EC001051 | ECLASS 14.0 | 27-40-02-05 |
| ECLASS 15.0 | 27-40-02-05 | | |

Drawings



KRN-M3/-0,75

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Crimping tools



Crimping tools for non-insulated connectors
Rolled cable lugs, tubular cable lugs, terminal pins,
parallel and serial connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

| | | | |
|------------|----------------------------|---|--|
| Type | HTN 21 | Version | |
| Order No. | 9014610000 | Pressing tool, Crimping tool for contacts, 0.5mm ² , 6mm ² , Indent | |
| GTIN (EAN) | 4008190152734 | crimp | |
| Qty. | 1 ST | | |