


ES APG 80 WM 6**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 400 mm²
- 360° revolving quick action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- Additional features for APG series:
 - electronic control and monitoring of the crimping process
 - Saving of all crimping cycles and error messages to internal memory
 - Reading of all cycles and error messages via USB

General ordering data

Version	6mm ² , WM crimp
Order No.	1502430000
Type	ES APG 80 WM 6
GTIN (EAN)	4050118310801
Qty.	1 items

ES APG 80 WM 6

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight 335.8 g

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Crimp inserts

Crimping width 7 mm Crimp cross-section copper 6
 Crimping width in mm 7

Description of contact

Conductor cross-section, max. AWG 10 Conductor cross-section, min. AWG 10
 Crimping range, max. 6 mm²

tool data crimping

Crimping type/profile WM crimp
 Cable lug cross section nominal 6 mm²

Classifications

ETIM 8.0	EC001282	ETIM 9.0	EC001282
ETIM 10.0	EC001282	ECLASS 14.0	21-04-90-90
ECLASS 15.0	21-04-90-90		

6 mm²6 mm²

The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KRN-M4/-6	Version
Order No.	1497150000	cable lug, terminal end,6 mm ² ,6 mm ² - 6 mm ²
GTIN (EAN)	4050118306767	
Qty.	100 ST	
Type	KRN-M5/-6	Version
Order No.	1497170000	cable lug, terminal end,6 mm ² ,6 mm ² - 6 mm ²
GTIN (EAN)	4050118306590	
Qty.	100 ST	
Type	KRN-M6/-6	Version
Order No.	1497180000	cable lug, terminal end,6 mm ² ,6 mm ² - 6 mm ²
GTIN (EAN)	4050118306729	
Qty.	100 ST	
Type	KRN-M8/-6	Version
Order No.	1497190000	cable lug, terminal end,6 mm ² ,6 mm ² - 6 mm ²
GTIN (EAN)	4050118306613	
Qty.	100 ST	
Type	KRN-M10/-6	Version
Order No.	1497200000	cable lug, terminal end,6 mm ² ,6 mm ² - 6 mm ²
GTIN (EAN)	4050118306385	
Qty.	100 ST	
Type	KRN-M12/-6	Version
Order No.	1497210000	cable lug, terminal end,6 mm ² ,6 mm ² - 6 mm ²
GTIN (EAN)	4050118306347	
Qty.	100 ST	
Type	KWN-M4/-6 90	Version
Order No.	1497220000	cable lug, terminal end,6 mm ² ,6 mm ² - 6 mm ²
GTIN (EAN)	4050118306477	
Qty.	100 ST	
Type	KWN-M5/-6 90	Version
Order No.	1496120000	cable lug, terminal end,6 mm ² ,6 mm ² - 6 mm ²
GTIN (EAN)	4050118305753	
Qty.	100 ST	
Type	KWN-M6/-6 90	Version
Order No.	1496130000	cable lug, terminal end,6 mm ² ,6 mm ² - 6 mm ²
GTIN (EAN)	4050118305982	
Qty.	100 ST	
Type	KWN-M8/-6 90	Version
Order No.	1496140000	cable lug, terminal end,6 mm ² ,6 mm ² - 6 mm ²
GTIN (EAN)	4050118306248	
Qty.	100 ST	

ES APG 80 WM 6

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	KWN-M10/-6 90	Version
Order No.	1496150000	cable lug, terminal end,6 mm ² ,6 mm ² - 6 mm ²
GTIN (EAN)	4050118305579	
Qty.	100 ST	
Type	KWN-M12/-6 90	Version
Order No.	1496170000	cable lug, terminal end,6 mm ² ,6 mm ² - 6 mm ²
GTIN (EAN)	4050118305869	
Qty.	100 ST	
Type	VSTN/-6	Version
Order No.	1494720000	cable lug, terminal end,6 mm ² ,6 mm ² ,None
GTIN (EAN)	4050118304190	
Qty.	100 ST	
Type	KP-M5/-6	Version
Order No.	1497840000	cable lug, terminal end,6 mm ²
GTIN (EAN)	4050118307405	
Qty.	100 ST	
Type	KP-M6/-6	Version
Order No.	1497850000	cable lug, terminal end,6 mm ²
GTIN (EAN)	4050118307245	
Qty.	100 ST	
Type	KP-M8/-6	Version
Order No.	1497860000	cable lug, terminal end,6 mm ²
GTIN (EAN)	4050118307238	
Qty.	100 ST	
Type	VPN/-6	Version
Order No.	1498610000	cable lug, terminal end,6 mm ² ,6 mm ² ,None
GTIN (EAN)	4050118307931	
Qty.	100 ST	