


**PF RS 90 GN 2000MM****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The RS 100 Profi offers you a flexible solution for your mounting needs, as both DIN rail mounting and wall mounting are possible. This versatility facilitates integration into different environments and applications. The housing can be used for the Eurocard PCB standard. The profile can be cut to size so that you can adapt it precisely to your specific requirements. For particularly heavy components, additional locking feet can be used to improve stability and thus increase the safety of your installation.

Another practical feature is the option of using a cover profile to protect large components.

**General ordering data**

Version	Profile housing, RS 90 Pale green, Extruded profile, Width: 2000 mm
Order No.	<a href="#">1505730000</a>
Type	PF RS 90 GN 2000MM
GTIN (EAN)	4050118315912
Qty.	2 M

## PF RS 90 GN 2000MM

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	15.7 mm	Depth (inches)	0.6181 inch
Height	83.6 mm	Height (inches)	3.2913 inch
Width	2000 mm	Width (inches)	78.74 inch
Net weight	250 g		

### Temperatures

Operating temperature	-50 °C...60 °C
-----------------------	----------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Material data

Surface finish	untreated
----------------	-----------

### General data

Colour	Pale green	Protection degree	IPO0
Colour chart (similar)	RAL 6021		

### Important note

Product information	<p>Dimensions of the PCB:          Thickness: 1.6 (± 0.2) mm, width: 79.8 (+0.2) mm          Dimension of RS section = PCB length - 4.5 mm          Example:          PCB length 160 mm, RS section = 155.5 mm          The article will soon no longer be available. Please do not carry out any further design-ins. The RS 70 and RS 100 profile series can be used as an alternative.</p>
---------------------	--

### Classifications

ETIM 8.0	EC002779	ETIM 9.0	EC002779
ETIM 10.0	EC002779	ECLASS 14.0	27-18-27-92
ECLASS 15.0	27-18-27-92		

PF RS 90 GN 2000MM

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

Drawings

www.weidmueller.com

