

CRIMPSET PZ 10 SQR D

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Crimp sets

General ordering data

Version	Assortment crimping tool, Crimping tool: PZ 10 SQR, Stripping tool: STRIPAX, Crimping range, min.: 0.14, Colour code: DIN
Order No.	1542290000
Type	CRIMPSET PZ 10 SQR D
GTIN (EAN)	4050118347128
Qty.	1 items
Packaging	Plastic box

CRIMPSET PZ 10 SQR D

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	261 mm	Depth (inches)	10.2756 inch
Height	57 mm	Height (inches)	2.2441 inch
Width	338 mm	Width (inches)	13.3071 inch
Net weight	1591.04 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	Lead 7439-92-1
SCIP	1eacbb3e-7931-4ebb-9179-f29fd9b50028

Technical data

Description of article	Set includes crimping tool up to 10 mm ² square, stripping tool and wire-end ferrules in DIN colour code
------------------------	---

Assortments

Crimping range, max.	10 mm ²	Crimping range, min.	0.14 mm ²
Packaging	Plastic box	Stripping tool	STRIPAX
Crimping tool	PZ 10 SQR	Colour code	DIN
Number of AEH	2900 pcs.		

Classifications

ETIM 8.0	EC000524	ETIM 9.0	EC000524
ETIM 10.0	EC000524	ECLASS 14.0	27-40-02-18
ECLASS 15.0	27-40-02-18		

CRIMPSET PZ 10 SQR D

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Tools



- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

General ordering data

Type	STRIPAX	Version	
Order No.	9005000000	Tools, Stripping and cutting tool	
GTIN (EAN)	4008190072506		
Qty.	1 ST		

Crimping tools



Crimping tools for wire end ferrules, with and without plastic collars

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Type	PZ 10 SQR	Version	
Order No.	1445080000	Crimping tool for wire-end ferrules, 0.14mm ² , 10mm ² , Square crimp	
GTIN (EAN)	4050118250152		
Qty.	1 ST		

packed loose in polythene bag



- supplied loose in polybag
- Weidmüller colour code
- DIN colour code

CRIMPSET PZ 10 SQR D

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

General ordering data

Type	H0,5/14D W	Version
Order No.	9019010000	Wire-end ferrule, Standard, 10 mm, 8 mm, white
GTIN (EAN)	4008190120931	
Qty.	500 ST	
Type	H0,75/14D GR	Version
Order No.	9019040000	Wire-end ferrule, Standard, 10 mm, 8 mm, grey
GTIN (EAN)	4008190099077	
Qty.	500 ST	
Type	H1,0/14D R	Version
Order No.	9019080000	Wire-end ferrule, Standard, 10 mm, 8 mm, red
GTIN (EAN)	4008190090623	
Qty.	500 ST	
Type	H1,5/14D SW	Version
Order No.	9019120000	Wire-end ferrule, Standard, 10 mm, 8 mm, black
GTIN (EAN)	4008190153793	
Qty.	500 ST	
Type	H2,5/15D BL	Version
Order No.	9019160000	Wire-end ferrule, Standard, 10 mm, 8 mm, blue
GTIN (EAN)	4008190028732	
Qty.	500 ST	
Type	H4,0/20D GR	Version
Order No.	9019200000	Wire-end ferrule, Standard, 14 mm, 12 mm, grey
GTIN (EAN)	4008190126575	
Qty.	500 ST	

Conductor nom. cross-section 6.0mm²



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Type	H6,0/20D GE	Version
Order No.	9019220000	Wire-end ferrule, Standard, 14 mm, 12 mm, yellow
GTIN (EAN)	4008190151607	
Qty.	100 ST	

CRIMPSET PZ 10 SQR D

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Conductor nom. cross-section 10mm²



10 mm²

- supplied loose in polybag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Type	H10,0/22D R	Version	
Order No.	9019240000	Wire-end ferrule, Standard, 15 mm, 12 mm, red	
GTIN (EAN)	4008190075385		
Qty.	100 ST		

Case



- Body of case made from unbreakable polypropylene
- Portable and uncluttered storage in minimum space
- With two sturdy sliding catches
- Assortment cases and boxes can be placed upright and can be stacked safely without any sliding
- can be subdivided with inserts

General ordering data

Type	KOFFER PSC4-01	Version	
Order No.	9028860000	Tools, Assortment box	
GTIN (EAN)	4032248304608		
Qty.	1 ST		