

**BUKO WM4 C RL**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**WM4 C photovoltaic connectors**

- one crimp contact for 4 mm<sup>2</sup> and 6 mm<sup>2</sup> cables
- TÜV approval according to the latest standard IEC 62852
- Can be loaded with a rated current of up to 35 A

**General ordering data**

Version	Photovoltaics, Plug-in connector, Socket connector
Order No.	<a href="#">1530770000</a>
Type	BUKO WM4 C RL
GTIN (EAN)	4050118335491
Qty.	4500 items

**BUKO WM4 C RL**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Net weight 2.45 g

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Classifications**

ETIM 8.0	EC002928	ETIM 9.0	EC002928
ETIM 10.0	EC002928	ECLASS 14.0	22-57-02-92
ECLASS 15.0	22-57-02-92		

**BUKO WM4 C RL**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Accessories****... for photovoltaic plug-in connectors**

After stripping the insulation, a suitable contact or wire end ferrule can be crimped onto the end of the cable. Crimping forms a secure connection between conductor and contact and has largely replaced soldering. Crimping denotes the creation of a homogeneous, permanent connection between conductor and connecting element. The connection can be made only with high-quality precision tools. The result is a secure and reliable connection both in mechanical and electrical terms. Weidmüller offers a wide range of mechanical crimping tools. Integral ratchets with release mechanisms guarantee optimum crimping. Crimped connections made with Weidmüller tools comply with international standards and regulations.

**General ordering data**

Type	CTF PV WM4	Version
Order No.	<a href="#">1222870000</a>	Photovoltaics, Crimping tool for photovoltaic contacts, Mechanical,
GTIN (EAN)	4050118006254	without interchangeable inserts
Qty.	1 ST	

**Accessories**

The dust protection cap "Dustcap VSSO" protects the Weidmüller and type 4 solar connectors against dust and dirt.

The "SafetyClip" protects the Weidmüller solar connectors against unintentional opening and can only be released using the special multi-tool.

**General ordering data**

Type	VSSO WM4 C	Version
Order No.	<a href="#">1254870000</a>	Photovoltaics, Flat design
GTIN (EAN)	4050118047479	
Qty.	100 ST	

**BUKO WM4 C RL**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Accessories****Tools**

- For flexible and solid conductors with special insulating materials
- High-quality stripping for industrial applications (complies with aircraft industry requirements)
- Specially shaped blades enable stripping of special types of insulation and conductor configurations
- Stripping length adjustable via end stop
- Very versatile thanks to interchangeable stripping units
- Stripping results reproduced accurately over and over again
- No damage to the conductor
- A long-lasting, reliable tool thanks to its sturdy design
- Integrated cutting function

**General ordering data**

Type	MULTI-STRIPAX PV	Version
Order No.	<a href="#">1190490000</a>	Photovoltaics, Plug-in connector
GTIN (EAN)	4032248973262	
Qty.	1 ST	

**WM4 C box plug-in connector****WM4 C photovoltaic connectors**

- one crimp contact for 4 mm<sup>2</sup> and 6 mm<sup>2</sup> cables
- TÜV approval according to the latest standard IEC 62852
- Can be loaded with a rated current of up to 35 A

**General ordering data**

Type	BUGH BOX WM4 C BT	Version
Order No.	<a href="#">1530630000</a>	Photovoltaics, Plug-in connector, female
GTIN (EAN)	4050118335453	
Qty.	100 ST	

**WM4 C panel plug****WM4 C photovoltaic connectors**

- one crimp contact for 4 mm<sup>2</sup> and 6 mm<sup>2</sup> cables
- TÜV approval according to the latest standard IEC 62852
- Can be loaded with a rated current of up to 35 A

**BUKO WM4 C RL**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Accessories****General ordering data**

Type	BUGH WM4 C BT	Version
Order No.	<a href="#">1530690000</a>	Photovoltaics, Plug-in connector, female
GTIN (EAN)	4050118335347	
Qty.	100 ST	