


## KSW 2,5 < 150MM SONDDR.

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com



Similar to illustration

KSW marking strips are used to identify multi-pole PCB plug-in connectors. Users can print them individually without being confined to a certain pitch.

- Smudge-proof labelling
- Strips 2.5 mm and 4 mm wide
- Simply stick on - finished
- Optimum adhesion
- PVC-free

### General ordering data

|            |  |
|------------|--|
| Version    | KSW, Terminal marker, 2.5 x 150 mm, Pitch in mm (P): 2.50 Weidmueller, white |
| Order No.  | <a href="#">1629940000</a>   |
| Type       | KSW 2,5 < 150MM SONDDR.  |
| GTIN (EAN) | 4008 190202842   |
| Qty.       | 1 items  |

## KSW 2,5 &lt; 150MM SONDDR.

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Height     | 2.5 mm | Height (inches) | 0.0984 inch |
| Width      | 150 mm | Width (inches)  | 5.9055 inch |
| Net weight | 1 g    |                 |             |

## Temperatures

|                             |        |
|-----------------------------|--------|
| Operating temperature range | 150 °C |
|-----------------------------|--------|

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## General data

|                                   |                           |                          |                  |
|-----------------------------------|---------------------------|--------------------------|------------------|
| Adhesive                          | Acrylate                  | Orientation of print     | horizontal       |
| Number per sheet                  | 20                        | Printing method          | Thermal transfer |
| Version                           | Self-adhesive             | Width                    | 150 mm           |
| Operating temperature range, max. | 150 °C                    | Colour                   | white            |
| Basic material                    | Polyester, PVC-free       | Colour of printing       | black            |
| Printed characters                | To customer specification | compatible printer       |                  |
| Operating temperature range       | 150 °C                    | Application/manufacturer | Weidmueller      |
| Imprint                           | Custom printing           |                          |                  |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000761    | ETIM 9.0    | EC000761    |
| ETIM 10.0   | EC000761    | ECLASS 14.0 | 27-28-11-01 |
| ECLASS 15.0 | 27-28-11-01 |             |             |