


## ESO 5 P DIN A4 GE

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



### General ordering data

Version	Terminal markers, Insert markers, 40 x 16.5 mm, yellow
Order No.	<a href="#">1670380000</a>
Type	ESO 5 P DIN A4 GE
GTIN (EAN)	4008190430702
Qty.	10 items
Delivery status	This article will no longer be available in the future.
Available until	2026-01-31T00:00:00+01:00
Alternative product	<a href="#">ELS 16/40 MM GE</a>

**ESO 5 P DIN A4 GE**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	1 mm	Depth (inches)	0.0394 inch
Height	40 mm	Height (inches)	1.5748 inch
Width	16.5 mm	Width (inches)	0.6496 inch
Net weight	13.7 g		

**Temperatures**

Operating temperature range -40...80 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%


**General data**

Material colour according to resistance code	4		
Orientation of print	horizontal and vertical		
Number per sheet	60		
Width	16.5 mm		
UL 94 flammability rating	HB		
Operating temperature range, max.	80 °C		
Operating temperature range, min.	-40 °C		
Colour	yellow		
Basic material	Polyester, PVC-free		
Printed characters	without		
Number of markers per packaging unit	Form of supply	Label sheet	
Number of markers per combination	1 Label sheet = Insert markers		
Operating temperature range	-40...80 °C		

**Classifications**

ETIM 8.0	EC000761	ETIM 9.0	EC000761
ETIM 10.0	EC000761	ECLASS 14.0	27-28-11-01
ECLASS 15.0	27-28-11-01		

**Drawings**



## Accessories

### WKM for inlay tags



The halogen-free, transparent pocket of the WKM offers outstanding protection against environmental influences. Thanks to firm fixation with cable ties, it is suitable for almost all wire cross-sections.

The pre-printed tags are simply inserted into the WKM holder and secured with a clip. WKM cable markers are the right solution for maximum efficiency in on-site marking. Your advantage when using WKM cables

- Paper and polyester labels can be printed individually with conventional office printers
- The robust design in combination with MultiCard ELS tags guarantees maximum protection against environmental influences

### General ordering data

Type	WKM 18/43	Version	
Order No.	<a href="#">1610700000</a>	WKM, Conductor and cable markers, 7 - 115 mm, 43 x 18 mm, Wire	
GTIN (EAN)	4008190204488	and cable markers, Transparent	
Qty.	50 ST		