


## PAGETAB 15/9

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration



PageTab are woven-fabric labels in sheet form. Except for the 8 x 20 version, all labels have a black border.

### General ordering data

|            |   |
|------------|---|
| Version    | Device markers, Device markers, 9 x 15 mm, yellow |
| Order No.  | <a href="#">1686160000</a>                        |
| Type       | PAGETAB 15/9                                      |
| GTIN (EAN) | 4008190492533                                     |
| Qty.       | 25 items  |

**Technical data**

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Dimensions and weights**

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 0.08 mm | Depth (inches)  | 0.0031 inch |
| Height     | 9 mm    | Height (inches) | 0.3543 inch |
| Width      | 15 mm   | Width (inches)  | 0.5906 inch |
| Net weight | 10 g    |                 |             |

**Temperatures**

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -29...93 °C |
|-----------------------------|-------------|

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

**General data**

|  |   |             |  |
|--|---|-------------|--|
| Adhesive                                     | Permanent acrylic copolymer               |             |  |
| Material colour according to resistance code | 4   |             |  |
| Number per sheet                             | 310                                       |             |  |
| Version                                      | Self-adhesive                             |             |  |
| Width  | 15 mm                                     |             |  |
| Operating temperature range, max.            | 93 °C                                     |             |  |
| Operating temperature range, min.            | -29 °C                                    |             |  |
| Colour                                       | yellow                                    |             |  |
| Basic material                               | Acrylic-coated fibre webbing              |             |  |
| Printed characters                           | without                                   |             |  |
| Number of markers per packaging unit         | 7750                                      |             |  |
| Number of markers per packaging unit         | Form of supply                            | Label sheet |  |
|  | Number of combinations per packaging unit | 25          |  |
|  | Number of markers per combination         | 310         |  |
| Number of markers per combination            | 1 Label sheet = 310 Device markers        |             |  |
| Operating temperature range                  | -29...93 °C                               |             |  |
| Imprint                                      | Neutral                                   |             |  |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001288    | ETIM 9.0    | EC001288    |
| ETIM 10.0   | EC001288    | ECLASS 14.0 | 27-28-11-04 |
| ECLASS 15.0 | 27-28-11-04 |             |             |

Drawings

