

EA-RING MS/M 20

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

| | |
|------------|---|
| Version | EA (earthing rings), Earthing ring, Miscellaneous, M 20, Brass, nickel-plated |
| Order No. | 1736490000 |
| Type | EA-RING MS/M 20 |
| GTIN (EAN) | 4008 190963590 |
| Qty. | 20 items |

EA-RING MS/M 20

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Height | 53.8 mm | Height (inches) | 2.1181 inch |
| Length | 53.8 mm | Length (inches) | 2.1181 inch |
| Net weight | 6.95 g | | |

Temperatures

Operating temperature

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 2bd73422-c6ea-4a92-b8e7-00964d1156f3 |

Certificate numbers cable gland

Identification Ex e II, II 2 GD, EEx d II

General information

| | | | |
|---------------------------|----------|--------------------------|----------------------|
| O.D. | 28.6 mm | Thickness | 1.50 mm |
| Cable gland | M 20 | Basic material | Brass, nickel-plated |
| External thread | M 20 | Inside diameter D2 | 7.00 mm |
| Gap, internal dimension B | 33.00 mm | Width, outer dimension C | 13.00 mm |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002317 | ETIM 9.0 | EC002317 |
| ETIM 10.0 | EC002317 | ECLASS 14.0 | 27-14-08-07 |
| ECLASS 15.0 | 27-14-08-07 | | |

EA-RING MS/M 20

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

