

VP M16-EXE SW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration

For sealing surplus threaded holes to maintain the IP class of protection

General ordering data

Version	VPK EX (Ex blanking plug in plastic), Blanking plug, in closed state, M 16, 15 mm, IP66, IP68, Polyamide
Order No.	1737070000
Type	VP M16-EXE SW
GTIN (EAN)	4008 190956547
Qty.	100 items
Delivery status	This article will no longer be available in the future.
Last order date	2024-08-31T00:00:00+02:00
Alternative product	VP M16/15 EX CR 7J BK

VP M16-EXE SW

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Height	19 mm	Height (inches)	0.748 inch
Length	19 mm	Length (inches)	0.748 inch
Diameter	16 mm	Wall thickness, min.	0.5 mm
Wall thickness, max.	14 mm	Net weight	2.67 g

Temperatures

Operating temperature -20 °C...80 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Technical properties

Protection degree IP54, IP66

Technical data

Protection degree IP54, IP66


Technical data

Colour Deep black Protection degree IP54, IP66

Classifications

ETIM 8.0	EC000451	ETIM 9.0	EC000451
ETIM 10.0	EC000451	ECLASS 14.0	27-14-08-05
ECLASS 15.0	27-14-08-05		

Drawings



VP M16-EXE SW

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Brass lock nuts, nickel-plated



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU M16 MS	Version	
Order No.	1736990000	SKMU MS (brass locknut), Locknut, M 16, 2.8 mm, Brass, nickel-	
GTIN (EAN)	4008 190956462	plated	
Qty.	100 ST		

Blanking plugs



For sealing surplus threaded holes to maintain the IP class of protection

General ordering data

Type	GWDR M16-NP	Version	
Order No.	1736230000	GWDR NP (flat gasket - neoprene), Sealing ring, M 16, Neoprene	
GTIN (EAN)	4008 190956028		
Qty.	50 ST		