


LM WO 37/25 GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration



Self-adhesive polyester labels which are suitable for A4 office laser printer.

General ordering data

Version	LaserMark, Conductor and cable markers, 3.4 - 4.8 mm, 37 x 25 mm, yellow
Order No.	1768430000
Type	LM WO 37/25 GE
GTIN (EAN)	4032248110070
Qty.	10 items

LM WO 37/25 GE

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	0.03 mm	Depth (inches)	0.001 inch
Height	37 mm	Height (inches)	1.4567 inch
Width	25 mm	Width (inches)	0.9842 inch
Net weight	8.98 g		

Temperatures

Operating temperature range -40...150 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Adhesive	Acrylate		
Material colour according to resistance code	4		
Number per sheet	55		
Type of printing	neutral		
Version	Self-adhesive		
Width	25 mm		
UL 94 flammability rating	V-0		
Operating temperature range, max.	150 °C		
Operating temperature range, min.	-40 °C		
Colour	yellow		
Halogen	No		
Basic material	Polyester film		
Printed characters	without		
Number of markers per packaging unit	550		
Number of markers per packaging unit	Form of supply	Label sheet	
	Number of combinations per packaging unit	10	
	Number of markers per combination	55	
Size of labelling field	37 x 8 mm		
Number of markers per combination	1 Label sheet = 55 Conductor and cable markers		
Operating temperature range	-40...150 °C		

Conductor and cable markers

Halogen	No	Conductor cross-section, max.	6 mm ²
Conductor cross-section, min.	2.5 mm ²	Conductor O.D., max.	4.8 mm
Conductor O.D., min.	3.4 mm	Text field width	35.5 mm
Text field height	8 mm	Conductor O.D.	3.4 - 4.8 mm
Cross-section for connected wire	2.5 - 6 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

Drawings

