


TEAP DLD2.5/PE DB**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Partition plates and end plates are essential accessories for terminal blocks. Partition plates provide optical and electrical separation of different potentials and functional groups, increasing safety and ensuring a clear structure inside the control cabinet. End plates close the terminal block row on the sides, protect against contact with live parts, and ensure a clean, stable finish. Both components are precisely matched to the respective Weidmüller terminal block series, contributing to safe, compliant, and professional wiring.

General ordering data

| | |
|------------|-------------------------------------------------------------------------------------|
| Version | Partition plate (terminal), dark beige, Height: 17.26 mm, Width: 1.2 mm, V-0, Wemid |
| Order No. | 1783810000 |
| Type | TEAP DLD2.5/PE DB |
| GTIN (EAN) | 4032248189922 |
| Qty. | 20 items |

TEAP DLD2.5/PE DB

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|----------|-----------------|-------------|
| Depth | 22.47 mm | Depth (inches) | 0.8846 inch |
| Height | 17.26 mm | Height (inches) | 0.6795 inch |
| Width | 1.2 mm | Width (inches) | 0.0472 inch |
| Net weight | 0.31 g | | |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|----------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -50 °C...75 °C |
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 120 °C |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Material data

| | | | |
|---------------------------|-------|--------|------------|
| Basic material | Wemid | Colour | dark beige |
| UL 94 flammability rating | V-0 | | |

System specifications

| | |
|---------|----------------------------|
| Version | End and intermediate plate |
|---------|----------------------------|

Additional technical data

| | | | |
|---------|-----|---------------------|-----------------|
| Snap-on | Yes | Installation advice | Direct mounting |
|---------|-----|---------------------|-----------------|

General

| | |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000886 | ETIM 9.0 | EC000886 |
| ETIM 10.0 | EC000886 | ECLASS 14.0 | 27-25-03-01 |
| ECLASS 15.0 | 27-25-03-01 | | |