


LM WO 25.4/57 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration



Self-adhesive polyester labels which are suitable for A4 office laser printer.

General ordering data

Version	LaserMark, Conductor and cable markers, 5.9 - 12.3 mm, 25.4 x 57 mm, white
Order No.	1768380000
Type	LM WO 25.4/57 WS
GTIN (EAN)	4032248110025
Qty.	10 items

LM WO 25.4/57 WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	0.03 mm	Depth (inches)	0.001 inch
Height	25.4 mm	Height (inches)	1 inch
Width	57 mm	Width (inches)	2.2441 inch
Net weight	10 g		

Temperatures

Operating temperature range -40...150 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Adhesive	Acrylate		
Material colour according to resistance code	9		
Number per sheet	35		
Type of printing	neutral		
Version	Self-adhesive		
Width	57 mm		
UL 94 flammability rating	V-0		
Operating temperature range, max.	150 °C		
Operating temperature range, min.	-40 °C		
Colour	white		
Halogen	No		
Basic material	Polyester film		
Printed characters	without		
Number of markers per packaging unit	350		
Number of markers per packaging unit	Form of supply	Label sheet	
	Number of combinations per packaging unit	10	
	Number of markers per combination	35	
Size of labelling field	25.4 x 18 mm		
Number of markers per combination	1 Label sheet = 35 Conductor and cable markers		
Operating temperature range	-40...150 °C		

Conductor and cable markers

Halogen	No	Conductor cross-section, max.	120 mm ²
Conductor cross-section, min.	25 mm ²	Conductor O.D., max.	12.3 mm
Conductor O.D., min.	5.9 mm	Text field width	25.4 mm
Text field height	18.5 mm	Conductor O.D.	5.9 - 12.3 mm
Cross-section for connected wire	25 - 120 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

Drawings

