

BEST**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

The component plug is used to integrate an electrical component in a disconnect terminal block. After soldering the electronic component, the plug can be integrated into the disconnection area of our disconnect terminal blocks and thus changes the disconnect terminal block into a modular terminal block with integrated electronic component.

General ordering data

| | |
|------------|-----------------------------|
| Version | Accessories, Component plug |
| Order No. | 1833100000 |
| Type | BEST |
| GTIN (EAN) | 4032248501014 |
| Qty. | 50 items |

BEST

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 63 mm | Depth (inches) | 2.4803 inch |
| Height | 49.5 mm | Height (inches) | 1.9488 inch |
| Width | 5 mm | Width (inches) | 0.1968 inch |
| Net weight | 3.72 g | | |

Temperatures

| | |
|---------------------|---------------|
| Ambient temperature | -5 °C...40 °C |
|---------------------|---------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Material data

| | | | |
|----------------|-------|--------|-------|
| Basic material | Wemid | Colour | beige |
|----------------|-------|--------|-------|

System specifications

| | |
|---------|------|
| Version | Plug |
|---------|------|

Additional technical data

| | | | |
|--------------------------|---------|---------------------|-----------------|
| Type of fixing | Plugged | Installation advice | Direct mounting |
| Explosion-tested version | No | Type of mounting | Plugged |

Conductors for clamping (rated connection)

| | |
|--------------------|---------------|
| Type of connection | Miscellaneous |
|--------------------|---------------|

Dimensions

| | |
|-----------------|---------|
| Pitch in mm (P) | 5.10 mm |
|-----------------|---------|

General

| | |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

Rating data

| | |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002018 | ETIM 9.0 | EC002018 |
| ETIM 10.0 | EC002018 | ECLASS 14.0 | 27-25-03-05 |
| ECLASS 15.0 | 27-25-03-05 | | |