

CC 15/17 MC SDR


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration



ClipCard device markers in MultiCard format are used for labelling electrical installations and switchgear systems, and offer an interesting alternative to engraving. Thanks to the proven MultiCard format, labelling is possible with PrintJet CONNECT or Plotter.

- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- Universal fixing
- Carrier (screwable or with cable ties)
- Tag rail (self-adhesive or screw fixing)
- Or self-adhesive tags

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	ClipCard, Device markers, 15 x 17 mm, Holder CC-H 15/17, To customer specification
Order No.	1876620000
Type	CC 15/17 MC SDR
GTIN (EAN)	4032248467136
Qty.	16 items

CC 15/17 MC SDR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	1 mm	Depth (inches)	0.0394 inch
Height	15 mm	Height (inches)	0.5906 inch
Width	17 mm	Width (inches)	0.6693 inch
Net weight	2.88 g		

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption	
REACH SVHC	No SVHC above 0.1 wt%	
Product Carbon Footprint	Cradle to gate	0.012 kg CO2 eq.

General data

Printing method	MC Laser	
Version	pluggable	
Width	17 mm	
UL 94 flammability rating	V-2	
Operating temperature range, max.	100 °C	
Operating temperature range, min.	-40 °C	
Colour	To customer specification	
Halogen	No	
Basic material	Polyamide 66	
Colour of printing	black	
Printed characters	Requires M-Print PRO File	
Number of markers per packaging unit	Form of supply	MultiCard
compatible printer	PRINTJET CONNECT , MCP BASIC 2 , MCP PLUS 2	
Number of markers per combination	1 MultiCard = Device markers	
Operating temperature range	-40...100 °C	
Application/manufacturer	Holder CC-H 15/17	

Device markers

Halogen	No
---------	----

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

CC 15/17 MC SDR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Accessories

www.weidmueller.com

Accessories



General ordering data

Type	CC-H 15/17	Version	
Order No.	1790430000	ClipCard, Accessories, 15 x 17 mm, black	
GTIN (EAN)	4032248215225		
Qty.	75 ST		
Type	ETO CC 15/17 TRANSPAR.	Version	
Order No.	1880850000	ClipCard, Accessories, 15 x 17 mm, Transparent	
GTIN (EAN)	4032248481224		
Qty.	10 ST		
Type	STR CC 15/17 TRANSPARENT	Version	
Order No.	1888310000	ClipCard, Accessories, 15 x 17 mm, Transparent	
GTIN (EAN)	4032248494187		
Qty.	80 ST		
Type	CC-RAIL 1000	Version	
Order No.	1790150000	ClipCard, Accessories, 1000 x 17 mm, Self-adhesive, black	
GTIN (EAN)	4032248213610		
Qty.	1 ST		
Type	CC-RAIL TRANSPARENT1000	Version	
Order No.	1790160000	ClipCard, Cover, 1000 x 19 mm, Transparent	
GTIN (EAN)	4032248213627		
Qty.	1 ST		