


BL-I/O JUMPER SET**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Example of use

Similar to illustration

No task is too small when creating the perfect solution. Connections form just one part of the overall process. Small details are often the key to the perfect solution in applications where potentials are tested, grouped or even isolated.

A system is not a system without small but useful details:

- Test plugs - ensure reliable pick-up from diagnostic sockets
- Cross-connectors - ensure a stable electrical distribution contact directly at the connection
- Compartment partition elements - divide a large number of male connectors into several separate socket connector channels
- Locks and clips - optional vibration-resistant clip-on connection or mounting for male and female connectors

In tandem with the manufacturing process and application - more accessories = smaller workload

General ordering data

Version	PCB plug-in connector, Accessories, Cross-connector, red / blue, Number of poles: 2
Order No.	1858970000
Type	BL-I/O JUMPER SET
GTIN (EAN)	4032248410590
Qty.	1 items
Product data	
Packaging	Box

BL-I/O JUMPER SET

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (UR) E60693

Dimensions and weights

Net weight 34.25 g

Environmental Product Compliance

RoHS Compliance Status Compliant

REACH SVHC No SVHC above 0.1 wt%

Material data

Colour red / blue

Colour chart (similar)

-

Contact material Cu-alloy

Storage temperature, min.

-40 °C

Storage temperature, max. 70 °C

Operating temperature, min.

-50 °C

Operating temperature, max. 100 °C

Temperature range, installation, min.

-25 °C

Temperature range, installation, max. 100 °C

Rated data acc. to IEC

tested acc. to standard IEC 60664-1, IEC 61984

Packing

Packaging Box

VPE length

47.00 mm

VPE width 45.00 mm

VPE height

20.00 mm

Important note

Product information 1 Set includes 25x red and 25x blue cross-connection

IPC conformity Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.

Notes • Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months

Classifications

ETIM 6.0 EC002943

ETIM 7.0 EC002943

ETIM 8.0 EC002943

ETIM 9.0 EC002943

ETIM 10.0 EC002943

ECLASS 9.0 27-44-04-92

ECLASS 9.1 27-44-04-92

ECLASS 10.0 27-44-04-92

ECLASS 11.0 27-46-04-06

ECLASS 12.0 27-46-04-06

ECLASS 13.0 27-46-04-06

ECLASS 14.0 27-46-04-06

ECLASS 15.0 27-46-04-06