

# **SCREWTY SET**



Weidmüller Interface GmbH & Co. KG

1

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com



#### The ideal tool for any application

Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

#### **General ordering data**

Version	Cable gland tool for M8, M12 lines and connec-
	tors
Order No.	<u>1910000000</u>
Туре	SCREWTY SET
GTIN (EAN)	4032248436842
Qty.	1 items
Packaging	Cardboard box

Catalogue status / Drawings



# **SCREWTY SET**



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

Dimensions a	nd weights
--------------	------------

Net weight 190.08 g

#### **Environmental Product Compliance**

RoHS Compliance Status	Not affected	
REACH SVHC	No SVHC above 0.1 wt%	

#### **Technical data**

Description of article

Screwed gland tool for

M8-, M12-cables and
connectors

#### **Important note**

Product information Included in delivery:

- Standard handle 1/4 inch
- Attachment M8 for moulded lines
- Attachment M8F for customisable connectors
- Attachment M12 for moulded lines
- Attachment M12F for customisable connectors

#### Classifications

ETIM 6.0	EC000149	ETIM 7.0	EC000149
ETIM 8.0	EC000149	ETIM 9.0	EC000149
ETIM 10.0	EC000149	ECLASS 9.0	21-04-50-03
ECLASS 9.1	21-01-90-90	ECLASS 10.0	21-04-50-03
ECLASS 11.0	21-01-90-90	ECLASS 12.0	21-01-90-90
ECLASS 13.0	21-01-90-90	ECLASS 14.0	21-01-90-90
ECLASS 15.0	21-01-90-90		

Catalogue status / Drawings 2

# **SCREWTY SET**



#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Accessories**

#### Screwty for M23 moulded cables and customisable connectors



The Screwty® attachment is suitable for customisable M23 round plug-in connectors and for overmoulded M23 round plug-in connectors, with an outside dimension of the knurled nut of  $26.2\pm0.3$  mm. The tightening torque is 2-2.5 Nm.

#### **General ordering data**

 Type
 SCREWTY M23
 Version

 Order No.
 1981560000
 Cable gland tool adapter for M23 lines and connectors

 GTIN (EAN)
 4032248677702

 Qty.
 1 ST

#### Screwty for M12 K-coded and L-coded overmolded cables



Weidmüller offers a wide range of tools and accessories for sensor-actuator cabling.

#### **General ordering data**

Туре	SCREWTY M12 K+L 2.5 O.SD	Version
Order No.	<u>2522710000</u>	Cable gland tool adapter for moulded M12 lines, K- and L-coded
GTIN (EAN)	4050118534566	
Qty.	1 ST	
Туре	SCREWTY M12 K+L O.SD	Version
Type Order No.	SCREWTY M12 K+L O.SD 2486610000	Version  Cable gland tool adapter for moulded M12 lines, K- and L-coded

Creation date 04.11.2025 05:01:31 MEZ

Catalogue status / Drawings 3