

SCREWTY SET**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The ideal tool for any application

Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

General ordering data

Version	Cable gland tool for M8, M12 lines and connectors
Order No.	191000000
Type	SCREWTY SET
GTIN (EAN)	4032248436842
Qty.	1 items
Packaging	Cardboard box

SCREWTY SET

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	190.08 g
------------	----------

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Screwed gland tool for M8, M12-cables and connectors
------------------------	--

Important note

Product information	Included in delivery: <ul style="list-style-type: none"> • Standard handle 1/4 inch • Attachment M8 for moulded lines • Attachment M8F for customisable connectors • Attachment M12 for moulded lines • Attachment M12F for customisable connectors
---------------------	--

Classifications

ETIM 8.0	EC000149	ETIM 9.0	EC000149
ETIM 10.0	EC000149	ECLASS 14.0	21-01-90-90
ECLASS 15.0	21-01-90-90		

SCREWTY SET

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Screwty for M23 moulded cables and customisable connectors



The Screwty® attachment is suitable for customisable M23 round plug-in connectors and for overmoulded M23 round plug-in connectors, with an outside dimension of the knurled nut of 26.2 ± 0.3 mm. The tightening torque is 2-2.5 Nm.

General ordering data

Type	SCREWTY M23	Version	
Order No.	1981560000		Cable gland tool adapter for M23 lines and connectors
GTIN (EAN)	4032248677702		
Qty.	1 ST		

Screwty for M12 K-coded and L-coded overmolded cables



Weidmüller offers a wide range of tools and accessories for sensor-actuator cabling.

General ordering data

Type	SCREWTY M12 K+L 2.5 O.SD	Version	
Order No.	2522710000		Cable gland tool adapter for moulded M12 lines, K- and L-coded
GTIN (EAN)	4050118534566		
Qty.	1 ST		
Type	SCREWTY M12 K+L O.SD	Version	
Order No.	2486610000		Cable gland tool adapter for moulded M12 lines, K- and L-coded
GTIN (EAN)	4050118497403		
Qty.	1 ST		